



2A Glass Passivated Single-Phase Bridge Rectifier

<p>特征/Features</p> <ul style="list-style-type: none"> ◆ 玻璃钝化芯片 Glass passivated chip ◆ 低反向漏电流 Low Reverse Leakage Current ◆ 高耐浪涌电流能力 High surge current capability 	<p>外形尺寸/Outline Dimensions</p> <p>Case: KBP Series Dimensions in millimeters</p>
<p>机械参数/Mechanical Data</p> <ul style="list-style-type: none"> ◆ 本体：塑封 Case: plastic package ◆ 标识/极性：本体标记 Marking / Polarity: Marked on Body ◆ 重量：约克 Weight: About 1.5 grams 	

极限值/Maximum Ratings and Thermal Characteristics @ Ta = 25 °C unless otherwise noted

符号 Symbol	特性 Characteristic	KBP2							单位 Unit
		005	01	02	04	06	08	10	
V _{RRM}	最大反向重复峰值电压 Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
I _F (AV)	平均整流输出电流 Average Forward Output Rectified Current@Ta =50°C	2							A
V _F	正向峰值电压 Forward Voltage Per Leg @IFM =2A	1.05							V
I _{FSM}	正向浪涌电流 Peak Forward Surge Current 8.3ms Single Half Sine-wave superimposed on rated load	45							A
I _R	反向漏电流 Maximum DC reverse current at rated DC blocking voltage per leg	5 500							uA
i ² t	热容值 Rating for fusing (t<8.3ms)	10							A ² S
R _{θJC}	热阻 Maximum thermal resistance per leg	15							°C/W
T _j , T _{STG}	结温, 存储条件 Operating Junction and storage temperature range	-55~150							°C

Note:

- (1) Junction to case with heatsink
- (2) Recommended mounting position is to bolt down on heatsink with silicone thermal compound for maximum heat transfer with M3 screw .



2A Glass Passivated Single-Phase Bridge Rectifier

■ 特性曲线 (典型) Characteristics(Typical)

Fig 1-forwardCurrent derating Curve
图1正向电流降额曲线




Fig.2-Maximum Non-Repetitive Surge Current
图2 最大不重复正向浪涌曲线




Fig.3-Typical Reverse Characteristics
图3.典型的反向特性






Fig.4-Typical Forward Characteristics
图4.典型的正向特性



2A Glass Passivated Single-Phase Bridge Rectifier



=Logo

**** =Date code marking

KBP210 = Marking code