




产品编号：[2242460620](#)

Product Description：Micro-Fit+ Versa
Color Vertical Header, Through Hole,
3.00mm Pitch, Dual Row, 6 Circuits, Tin
(Sn) Plating, Glow-Wire Capable, Red, Tray

系列号：224246

状态：Active

Product Category：PCB Headers and
Receptacles



文件和资源

图纸

[图纸 2242460620_sd.pdf](#)

[包装设计图 2068320000-PK-000.pdf](#)

3D 模型和设计文件

[3D模型 2242460620_stp.zip](#)

规格

[应用规格 2064600001-AS-000.pdf](#)

[产品规格 2064600000-PS-000.pdf](#)

[测试摘要 2064600000-TS-000.pdf](#)

产物环境合规

合规

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

[多部分产品合规性声明](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[多部分行业合规性文件](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

欧盟 RoHS 合格证书

产品详情

常规

状态	活动
类别	PCB Headers and Receptacles
系列	224246
说明	Micro-Fit+ Versa Color Vertical Header, Through Hole, 3.00mm Pitch, Dual Row, 6 Circuits, Tin (Sn) Plating, Glow-Wire Capable, Red, Tray
应用	Power, Wire-to-Board
元件类型	PCB Header
产品系列	Micro-Fit+ Connector System
产品名称	Micro-Fit+ Versa Color
UPC	196823364976

电气

每触点最大电流	12. 5A
电压 - 最大	600V AC (RMS) /DC

物理

断开	否
回路数（已载入）	6
电路数（最多）	6
颜色-树脂	红色
耐用性(插拔次数) - 最多次数	25
先接后断	否
符合灼热丝规范	是
插接极性	是
锁定插接部位	是

材料 - 金属	High Copper Alloy
材料 - 接合部位电镀	Tin
材料 - 终端电镀	Tin
材料 - 树脂	Liquid Crystal Polymer
净重	0.789/g
行数	2
方向	垂直
包装形式	Tray
PC 焊脚长度	3.18mm
推荐的 PCB 厚度	1.57mm
间距 - 插配接口	3.00mm
间距 - 终端界面	3.00mm
有极性的插配件	是
PCB 极性	是
有护墙的	是
运行温度范围	-40° to +105° C
终端界面类型	Through Hole

可配插/可连接使用的产品

可配插部件

描述	产品编号
Micro-Fit+ Dual Row Receptacle Housings	<u>206461</u>