

## 150V N-Channel Power MOSFET

### Description


IRFP4568PBF, the N-channel Enhanced Power MOSFETs, is obtained by advanced double trench technology which reduce the conduction loss, improve switching performance and enhance the avalanche energy. This is suitable device for BMS and high current switching applications.

### General Features

- ①  $V_{DS}=150V$ ,  $R_{dson}<6m\Omega$  @ $V_{GS}=10V$ ,  $I_D=180A$  (Typ:5.2m $\Omega$ )
- ② Fast Switching
- ③ Low On-Resistance ( $R_{DS(on)}\leq 6m\Omega$ )
- ④ Low Gate Charge
- ⑤ Low Reverse transfer capacitances
- ⑥ High avalanche ruggedness
- ⑦ RoHS product

### Application

- ① BMS
- ② High Current Switching Applications.



### Package Marking And Ordering Information:

Ordering Codes	Package	Product Code	Packing
IRFP4568PBF	TO-247	IRFP4568PBF	Tube

### ABSOLUTE RATINGS(at TC=25°C, unless otherwise specified)

Symbol	Parameter	Rating	Units
$V_{DSS}$	Drain-Source Voltage	150	V
$I_D$	Continuous Drain Current, Silicon Limited	140	A
	Continuous Drain Current, Package Limited	180	A
	Continuous Drain Current @ $T_c=100^\circ C$ , Silicon Limited	79.2	A
$I_{DM}$ <sup>Note1</sup>	Pulsed Drain Current	500	A
$V_{GS}$	Gate-Source Voltage	$\pm 20$	V
$E_{AS}$ <sup>Note2</sup>	Avalanche Energy	784	mJ
$P_D$	Power Dissipation	208.3	W
	Derating Factor above 25°C	1.66	W/°C
$T_J, T_{stg}$	Operating Junction and Storage Temperature Range	150, -55 to 150	°C
$T_L$	Maximum Temperature for Soldering	260	°C

Note1: Repetitive Rating: Pulse width limited by maximum junction temperature

Note2: L=0.5mH,  $I_{as}=56A$ , Start  $T_J=25^\circ C$

## Thermal characteristics

Symbol	Parameter	Max	Units
$R_{\theta JC}$	thermal resistance, Junction-Case	0.6	$^{\circ}\text{C}/\text{W}$
$R_{\theta JA}$	thermal resistance, Junction-Ambient	62.5	$^{\circ}\text{C}/\text{W}$

## Electrical Characteristics(at $T_C=25^{\circ}\text{C}$ , unless otherwise specified)

OFF Characteristics						
Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
$V_{DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0\text{V}$ , $I_D=250\mu\text{A}$	150	165	--	V
$I_{DSS}$	Drain-Source Leakage Current	$V_{DS}=150\text{V}$ , $V_{GS}=0\text{V}$	--	--	1	$\mu\text{A}$
		$V_{DS}=120\text{V}$ , $V_{GS}=0\text{V}$ @ $T_C=125^{\circ}\text{C}$	--	--	100	$\mu\text{A}$
$I_{GSS(F)}$	Gate-Source Forward Leakage	$V_{GS}=+20\text{V}$	--	--	100	nA
$I_{GSS(R)}$	Gate-Source Reverse Leakage	$V_{GS}=-20\text{V}$	--	--	-100	nA

ON Characteristics						
Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
$R_{DS(on)}$	Drain-Source On-Resistance	$V_{GS}=10\text{V}$ , $I_D=50\text{A}$	--	5.2	6	$\text{m}\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}$ , $I_D=250\mu\text{A}$	3	4	5	V

Pulse width  $t_p \leq 300\mu\text{s}$ ,  $\delta \leq 2\%$

Dynamic Characteristics						
Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
$C_{iss}$	Input Capacitance	$V_{DS}=75\text{V}$ , $V_{GS}=0$ , $f=1\text{MHz}$	--	6650	--	pF
$C_{oss}$	Output Capacitance		--	572	--	
$C_{rss}$	Reverse Transfer Capacitance		--	14	--	
$Q_g$	Total Gate Charge	$V_{DD}=75\text{V}$ , $I_D=50\text{A}$ , $V_{GS}=10\text{V}$	--	98	--	nC
$Q_{gs}$	Gate-Source charge		--	45	--	
$Q_{gd}$	Gate-Drain charge		--	21	--	
$R_G$	Gate resistance	$V_{GS}=0$ , $V_{DS}=0$		0.7		$\Omega$

**Switching Characteristics**

Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
$t_{d(on)}$	Turn-On Delay Time	$V_{DD}=75V, V_{GS}=10V,$ $R_G=3\Omega,$ Resistive Load	--	19	--	ns
$t_r$	Rise Time		--	20	--	
$t_{d(off)}$	Turn-Off Delay Time		--	68	--	
$t_f$	Fall Time		--	14	--	

**Source-Drain Diode Characteristics**

Symbol	Parameter	Test Conditions	Values			Units
			Min	Typ	Max	
$I_S$	Continuous Source Current		--	--	180	A
$I_{SM}$	Maximum Pulsed Current		--	--	500	A
$V_{SD}$	Diode Forward Voltage	$V_{GS}=0V, I_S=50A$	--	--	1.2	V
$T_{rr}$	Reverse Recovery Time	$I_S=20A, V_{GS}=0,$ $di/dt=100A/\mu s$	--	90	--	ns
$Q_{rr}$	Reverse Recovery Charge		--	1090	--	nC

Characteristics Curves

Figure 1. Safe Operating Area




Figure 2. Maximum Power Dissipation vs Case Temperature




Figure 3. Maximum Continuous Drain Current vs Case Temperature




Figure 4. Typical Output Characteristics




Figure 5. Transient Thermal Impedance




Figure 6. Typical Transfer Characteristics




Figure 7. Source-Drain Diode Forward Characteristics




Figure 8. Drain-Source On-Resistance vs Drain Current




Figure 9. Normalized On-Resistance vs Junction Temperature




Figure 10. Normalized Threshold Voltage vs Junction Temperature




Figure 11. Normalized Breakdown Voltage vs Junction Temperature




Figure 12. Capacitance Characteristics





Figure 13. Typical Gate Charge vs Gate-Source Voltage



Test Circuit and Waveform

Figure 14. Resistive Switching Test Circuit




Figure 15. Resistive Switching Waveforms




Figure 16. Gate Charge Test Circuit




Figure 17. Gate Charge Waveforms




Figure 18. Diode Reverse Recovery Test Circuit




Figure 19. Diode Reverse Recovery Waveform




Figure 20. Unclamped Inductive Switching Test Circuit






Figure 21. Unclamped Inductive Switching Waveform



Package Description



Items	Values (mm)	
	MIN	MAX
A	4.90	5.16
A1	2,27	2.53
A2	1.85	2.11
B	1.07	1.33
B1	1.90	2.41
B2	1.75	2.15
B3	2.87	3.38
B4	2.87	3.13
C	0.55	0.68
D	20.82	21.10
D1	16.25	17.65
D2	1.05	1.35
E	15.70	16.03
E1	13.10	14.15
E2	3.68	5.10
E3	1.68	2.60
e	5.44	
L	19.80	20.31
L1	4.17	4.47
ΦP	3.50	3.70
Q	5.49	6.00
S	6.04	6.30

TO-247 Package



迈诺斯科技

IRFP4568PBF

**NOTE:**

1. Exceeding the maximum ratings of the device in performance may cause damage to the device, even the permanent failure, which may affect the dependability of the machine. Please do not exceed the absolute maximum ratings of the device when circuit designing.
2. When installing the heat sink, please pay attention to the torsional moment and the smoothness of the heat sink.
3. MOSFETs is the device which is sensitive to the static electricity, it is necessary to protect the device from being damaged by the static electricity when using it.
4. Shenzhen Minos reserves the right to make changes in this specification sheet and is subject to change without prior notice.

**CONTACT:**

**深圳市迈诺斯科技有限公司（总部）**

地址：深圳市福田区华富街道田面社区深南中路4026号田面城市大厦16D

邮编：518025

电话：0755-83273777