






标 记 MARK	ECN编号/变更内容 ECN NO/DEFINITION	修 改 REVISE	日 期 DATE	核 准 APPROVE

CKI	DIM A	DIM B	DIM C	DIM D
4	3.00	4.40	5.20	7.00
5	4.00	5.40	6.20	8.00
6	5.00	6.40	7.20	9.00
7	6.00	7.40	8.20	10.00
8	7.00	8.40	9.20	11.00
9	8.00	9.40	10.20	12.00
10	9.00	10.40	11.20	13.00
11	10.00	11.40	12.20	14.00
12	11.00	12.40	13.20	15.00
13	12.00	13.40	14.20	16.00
14	13.00	14.40	15.20	17.00
15	14.00	15.40	16.20	18.00
16	15.00	16.40	17.20	19.00
17	16.00	17.40	18.20	20.00
18	17.00	18.40	19.20	21.00
19	18.00	19.40	20.20	22.00
20	19.00	20.40	21.20	23.00



- 技术指标:
- 1. 温度范围: -25℃~85℃
 - 2. 额定电压: 50V, AC/DC
 - 3. 耐 压: 500V AC/minute
 - 4. 接触电阻: ≤20mΩ
 - 5. 绝缘电阻: ≥100MΩ
 - 6. 额定电流: 1A, AC, DC



1	胶壳	PA66	白色	
序 号	品 名	材 质	电镀/颜色	备 注



深圳市虹成电子有限公司

品 名 TITLE	胶壳
料 号 PART NO	HC-SHD1.0-2x7Y

GENERAL TOLERANCES (UNLESS SPECIFIED)	比 列 SCALE	1:1		
X. ±0.50 .XX ±0.10	单 位 UNIT	MM	制 图 DRAW	AhYe
.X ±0.20 .XXX ±0.05	张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云
ANGLES ±1°	版 本 REV	A	批 准 APPROVE	赵亮亮

