











NOTES:

- 1) MATERIAL:
INSULATOR: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: BLACK .
CONTACTS: PHOSPHOR BRONZE
- 2) PLATING:
CONTACT AREA: 0.381um MIN. GOLD PLATING
SOLDER TAILS: 0.025um MIN. GOLD FLASH OVER 1.27um. NICKEL
- 3) COPLANARITY TO BE WITHIN 0.10
- 4) PACKAGED STANDARD IN TRAYS. 105 PCS. PER TRAY.
- 5) TAPE AND REEL PACKAGING OPTIONAL. 500 PCS PER REEL. ADD -T TO PART NUMBER.

SECT. A-A




TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAXCONN ENTERPRISE LIMITED		TITLE: SFP+ 20p SMT CONNECTOR					
LINEAR	ANGLES			PART NO. M42F-08P-020-P002G					
X,±0.40	X°,±			DWG NO. M42F1605071					
.X±0.30	.X°±	APPD: Jason	MAT'L:		UNITS	SCALE	SHEET	REV	
.XX±0.20	.XX°±	CHKD: Schumi	FINISH:		MM	1 : 1	1 OF 3	1	
.XXX±0.10	.XXX°±	DRWN: Lucy	Q'TY:						



REV	See Sheet 1	NAME	DATE
ECN NO.			

TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAXCONN ENTERPRISE LIMITED	
LINEAR	ANGLES		
X±0.40	X°±	APPD: Jason	MAT'L:
.X±0.30	.X°±	CHKD: Schumi	FINISH:
.XX±0.20	.XX°±	DRWN: Lucy	Q'TY:
.XXX±0.10	.XXX°±		

TITLE:		SFP+ 20p SMT CONNECTOR			
PART NO.		M42F-08P-020-P002G			
DWG NO.		M42F1605071			
	UNITS	SCALE	SHEET	REV	
	MM	2 : 1	2 OF 3	1	



TOP VIEW OF BOARD

BOTTOM VIEW OF BOARD

RECOMMENDED LAYOUT DETAIL
MATING TRANSCEIVER PCB

				TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAXCONN ENTERPRISE LIMITED		TITLE: SFP+ 20p SMT CONNECTOR				
				LINEAR	ANGLES			PART NO. M42F-08P-020-P002G				
				X,±0.40	X°,±			DWG NO. M42F1605071				
				.X,±0.30	.X°,±	APPD: Jason	MAT'L:		UNITS	SCALE	SHEET	REV
	See Sheet 1			.XX,±0.20	.XX°,±	CHKD: Schumi	FINISH:					
REV	ECN NO.	NAME	DATE	.XXX,±0.10	.XXX°,±	DRWN: Lucy	Q'TY:		MM	2 : 1	3 OF 3	1