


DWG NO 608695

UNIT OF MEASURE	A	B	C	D	E	G	L	MAX BUNDLE DIA.	MIN. TENSILE STRENGTH
INCHES	.788	.348	.187	.239	.055	.212	16.06	4.0	50 lbs.
MM	20.02	8.84	4.75	6.07	1.40	5.38	408.	101.6	22.68 kg.



NOTES:

1. MOISTURIZED 1 TO 2.5% WATER.
2. PACKAGED IN HEAT SEALED 3 MIL POLYBAG WITH LABEL PER DWG 404707.



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

APC ENGINEERING

JUL 13 1990

ISSUED BY *Chen*CUSTOMER
DRAWING
UNPUBLISHED

OBSOLETE

1-608695-9	NATURAL-100 PCS. SMTY4C
2-608695-9	NATURAL-1000 PCS. SMTY4M
1-608695-0	BLACK-100 PCS. SMTY4CB
2-608695-0	BLACK-1000 PCS. SMTY4MB

LOC D	DWG SIZE	PART No.	DESCRIPTION	ITEM NO
DIST 1	REVISION OF EACH ASSY NO. (WHEN BLANK, USE DWG REVISION)			
QTY. REQ'D. PER ASSY.		PARTS LIST		
		MATERIAL NYLON 6/6	HEAT TREAT	FINISH
		DIMENSIONS ARE IN INCHES	DRAWN BY: AD-TEK/VL	DATE: 7/3/90
		TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHECK BY: BJM	RELEASE: 7 Harned 7/5/90
		2 PL DEC ±		
		3 PL DEC ± .030		
		4 PL DEC ±		
		ANGLES ±		
		SURF TEXTURE: J		
		REMOVE BURRS, BREAK SHARP EDGES, .015 R. MAX.		
		SCALE: A	DRAWING No.: 608695	
			SHEET: 1 OF 1	
			REV: 01	
P	F	LTR	REVISION RECORD	
		APP	DATE	
		KK	28NOV 89	
		7m	7/90	
		O1	REVISED PER ECO-09-026444	
		0	ECN 062890	

THIS INFORMATION IS CONFIDENTIAL AND IS DISCLOSED TO YOU ON CONDITION THAT NO FURTHER DISCLOSURE IS MADE BY YOU TO OTHER THAN AMP PERSONNEL WITHOUT WRITTEN AUTHORIZATION FROM AMP INCORPORATED, HARRISBURG, PA