

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT 2010 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
DW	—

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECR-20-007978	31MAY2021	R.M	S.Z







RECOMMENDED P.C.B LAYOUT
TOP VIEW(TOLERANCE: ±0.05)


NOTES:
1. MATERIAL:
 1.1 HOUSING: SEE TABLE
  (PA66 WITH 30% G.F, UL94 V-0, BLACK OR WHITE COLOR.
  OR LCP WITH 30% G.F, UL94 V-0, BLACK COLOR.)
 1.2 CONTACT: BRASS, T=0.25.
 1.3 SHELL: SPCC.
 1.4 REAR SHELL: SPCC.
 1.5 SPRING: SPCC.
2. FINISH:
 2.1 CONTACT:
  GOLD PLATING (SEE TABLE) ON CONTACT AREA,
  2.54um [100u"] MIN. BRIGHT-TIN PLATING ON SOLDER TAIL AREA,
  1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.
 2.2 SHELL:
  2.54um [100u"] MIN. BRIGHT-TIN PLATING,
  1.27um [50u"] MIN. NICKEL UNDERPLATING OVERALL.
 2.3 REAR SHELL: 1.27um [50u"] MIN. NICKEL PLATING.
 2.4 SPRING : 1.27um [50u"] MIN. NICKEL PLATING.
3. RECOMMENDED P.C.B THICKNESS :1.6mm.
4. WAVE SOLDER CAPABLE TO 265°C PER TE SPEC. 109-202, CONDITION B.
5. THE SPRING IS OPTIONAL.
C2 6. OBSOLETE








6	0.381um [15u"]	W/ O	PA66(BLACK)	1-1775468-2
6		W/	PA66(BLACK)	1-1775468-1
6	GOLD FLASH	W/	PA66(WHITE)	1775468-3
	GOLD FLASH	W/ O	LCP	1775468-2
6	GOLD FLASH	W/	PA66	1775468-1
	MIN. GOLD THICKNESS	5 SPRING	HSG MATERIAL	PART NUMBER





MOUNTING PANEL CUTOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.3
2 PLC	± 0.2
3 PLC	± 0.15
4 PLC	± -
ANGLES	± 3°

MATERIAL: SEE NOTE

FINISH: SEE NOTE

DWN	J. LEE 30MAR2007
CHK	S. HOU 30MAR2007
APVD	W.J. KE 30MAR2007
PRODUCT SPEC	108-57519
APPLICATION SPEC	—
WEIGHT	5.31 GRAMS

TE Connectivity

NAME: USB A TYPE, RECEPTACLE DUAL PORT, R/A, DIP CONNECTOR

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1775468	—

CUSTOMER DRAWING | SCALE — | SHEET 1 OF 2 | REV C2


1470-19 (1/08)


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT 2010 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST
DW	—


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			












NOTES:

1. DIMENSION:
   TRAY: L= 270, W=235, H=25
   SHIPPING CARTON: L= 485, W=280, H=210
2. QUANTITY: (SEE TABLE)
3. CARTON WEIGHT: (SEE TABLE)
4. PE BAGS SEALED AND ADD DESICCANT.



11.6	10.6	100	20	2000
GROSS WEIGHT	NET WEIGHT	PCS/ TRAY	TRAYS/ CARTON	PCS/ CARTON

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL –

FINISH –

DWN	–
CHK	–
APVD	–
PRODUCT SPEC	–
APPLICATION SPEC	–
WEIGHT	–

TE Connectivity

NAME
USB A TYPE, RECEPTACLE
DUAL PORT, R/A, DIP CONNECTOR

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-1775468	–

CUSTOMER DRAWING | SCALE – | SHEET 2 OF 2 | REV C2