207489-1 ✔ ACTIVE

AMP | AMP CPC

TE Internal #: 207489-1

Boot, Thermoplastic, Black, Shell Size 11, .15 - .25 in [3.81 - 6.35 mm] Cable Entry, AMP CPC

View on TE.com >

Connectors > Connector Accessories > Connector Strain Relief







Strain Relief Accessory Type: **Boot**

Primary Product Material: **Thermoplastic**

Primary Product Color: **Black**

Compatible With Connector Shell Size: **11**

Cable Entry Diameter: **3.81 - 6.35 mm [.15 - .25 in]**

Features

Product Type Features

Strain Relief Accessory Type	Boot

Body Features

Primary Product Material	Thermoplastic
Primary Product Color	Black

Dimensions

Cable Entry Diameter	3.81 - 6.35 mm[.15 - .25 in]

Operation/Application

Compatible With Connector Shell Size	11

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # CAT-AM71-C83998M
CPC Connectors, Series 2



TE Part # CAT-AM71-C83998F
Connectors with Posted Pin Contacts, CPC Series 1



TE Part # CAT-AM71-C83998J
Cable/Panel Mount Connector, CPC Series 1



TE Part # CAT-AM71-C83998DD
Connectors, CPC Series 2, with Posted Contacts



TE Part # 208130-1
CPC RECPT ASSEMBLY SIZE 11-4

Also in the Series | AMP CPC



Circular Power Connectors(458)



Connector Backshells(1)



Connector Caps & Covers(16)




Connector Contacts(6)

Connector Hardware(12)

Connector Seals & Cavity Plugs(36)

Connector Strain Relief(60)

Insertion & Extraction Tools(1)



Sealing Sleeves(2)

Customers Also Bought

TE Part # 206429-1
Circular Connector, Environmentally Sealed, CPC Series 6


TE Part # 207387-1
CABLE GRIP,SZ 17,CPC

TE Part # 3-60874-2
058 PCB PIN GPPHBZ

TE Part # 4-2176379-4
RQ 0805 301R 0.1% 10PPM 5K RL



TE Part # 6-2176379-3
RQ 0805 475R 0.1% 10PPM 5K RL



TE Part # 879514-000
202K132-4/42-0

TE Part # 807767N001
222D152-4-60-0-CS5078

Documents

Product Drawings

FLEXIBLE CABLE BOOT, SIZE 11

English

CAD Files

Customer View Model

ENG_CVM_207489-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_207489-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_207489-1_B.3d_stp.zip

English

3D PDF

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_207489-1_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_207489-1_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_207489-1_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditionsof use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English

CSA Certificate

English