Specifications







Eaton FWX-15A14F

Eaton Bussmann series FWX high speed fuse, 15A, 200 kAIC Vac, 50 kAIC at 250 Vdc, Non Indicating, High speed fuse, Ferrule end X ferrule end

General specifications	
PRODUCT NAME	Eaton Bussmann series high speed cylindrical fuse
CATALOG NUMBER	FWX-15A14F
UPC	051712795579
EAN	5027590501347
PRODUCT LENGTH/DEPTH	55 mm
PRODUCT HEIGHT	32 mm
PRODUCT WIDTH	73 mm
PRODUCT WEIGHT	22.4 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized
GLOBAL CATALOG	FWX-15A14F
PRODUCT TYPE	High speed cylindrical fuse

Powering Business Worldwide

Product specifications

AMPERAGE RATING	1500 A
ACCESSORIES	• CH14 Modular fuse holder • FW14-PCB
BREAKING CAPACITY	200 kA
FREQUENCY RATING - MAX	62 Hz
FREQUENCY RATING - MIN	45 Hz
FUSE INDICATOR	Other
RELEASE CHARACTERISTIC	Other
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	14 x 51 mm
RATED VOLTAGE AC	250 V
RATED VOLTAGE DC	250 V
CLASS	Class aR
CLEARING (I2T)	83 at 250 V
WATT LOSSES	3.8 W
FUSE SHAPE	Cylindrical
PRE ARC (I2T)	14
INTERRUPT RATING	200 kAIC
CONNECTION	Ferrule end x ferrule end
CONSTRUCTION SIZE	14 mm x 51 mm
MATERIAL	Ceramic
PACKAGING TYPE	Standard
VOLTAGE RATING	700 V
TYPE	High speed fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, Power converters/rectifiers
FUSE TYPE	FWX-A14F
BREAKING CAPACITY AT NOMINAL VOLTAGE, AC	200 kA
BREAKING CAPACITY AT NOMINAL VOLTAGE, DC	50 kA

Resources

CATALOGS	eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf Bussmann series complete full line catalog no. 1007
MCAD MODEL	eaton-hs-round-body-fuses-mcad-3d-models-fwh-14f.stp
TECHNICAL DATA SHEETS	eaton-bussmann-series-fwx-ferrule-high-speed-fuses-datasheet-720006-en-gb.pdf

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.