

Features

- ❑ Transient protection for high-speed data lines
 - IEC 61000-4-2 (ESD) $\pm 30\text{kV}$ (Air)
 - $\pm 30\text{kV}$ (Contact)
 - IEC 61000-4-4 (EFT) 40A (5/50 ns)
 - IEC 61000-4-5 (Surge) 10A (8/20 μs)
- ❑ Package optimized for high-speed lines
- ❑ Provides protection for one line pair
- ❑ Low capacitance: 1.5pF @ 3.3V (Typical)
- ❑ Low leakage current: 0.01 μA @ V_{RWM} (Typical)
- ❑ Low operating and clamping voltage
- ❑ Each I/O pin can withstand over 1000 ESD strikes for $\pm 8\text{kV}$ contact discharge

Description

TS0301VB is a low-capacitance Transient Voltage Suppressor (TVS) array designed to provide electrostatic discharge (ESD) protection for high-speed data interfaces. With typical capacitance of 1.5pF only, TS0301VB is designed to protect parasitic-sensitive systems against over-voltage and over-current transient events. It complies with IEC 61000-4-2 (ESD), Level 4 ($\pm 15\text{kV}$ air, $\pm 8\text{kV}$ contact discharge), IEC 61000-4-4 (electrical fast transient - EFT) (40A, 5/50 ns), IEC 61000-4-5 (Surge) (10 A, 8/20 μs), very fast charged device model (CDM) ESD and cable discharge event (CDE), etc.

TS0301VB is in a uDFN-2L package. Each TS0301VB device can protect one high-speed line pair. The “flow-thru” design minimizes trace inductance and reduces voltage overshoot associated with ESD events. The combined features of low capacitance and high ESD robustness make TS0301VB ideal for portable applications such as cellular phones and MP3 players. The low clamping voltage of the TS0301VB guarantees a minimum stress on the protected IC.


Applications

- ❑ Portable instruments
- ❑ Desktops, Servers and Notebooks
- ❑ Cellular Phones
- ❑ MP3 Players
- ❑ Keypads, Side Keys


Mechanical Characteristics

- ❑ uDFN-2L package
- ❑ Flammability Rating: UL 94V-0
- ❑ Marking: Part number
- ❑ Packaging: Tape and Reel

Circuit Diagram



Pin Configuration




Absolute Maximum Rating







Symbol	Parameter	Value	Units
I_{PP}	Peak Pulse Current (8/20 μ s)	10	A
P_{PK}	Peak Pulse Power (8/20 μ s)	100	Watts
V_{ESD}	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	± 30 ± 30	kV
T_{OPT}	Operating Temperature	-45 to +85	°C
T_{STG}	Storage Temperature	-55 to +150	°C

Electrical Characteristics (T = 25°C)

Symbol	Parameter
V_{RWM}	Nominal Reverse Working Voltage
I_R	Reverse Leakage Current @ V_{RWM}
V_{tl}	Trigger Voltage
I_{tl}	Trigger Current @ V_{tl}
V_h	Holding Voltage
I_h	Holding Current @ V_h
V_C	Clamping Voltage @ I_{PP}
I_{PP}	Maximum Peak Pulse Current
C_{ESD}	Parasitic Capacitance
C_{Δ}	Variation in C_{ESD} with Reverse Bias




Symbol	Test Condition	Minimum	Typical	Maximum	Units
V_{RWM}				3.3	V
I_R	$V_{RWM} = 3.3V, T = 25^{\circ}C$		0.01	0.05	μA
V_{tl}	$I_{tl} = 10nA$	6.0		7.0	V
V_h	$I_h = 10mA$	3.5		4.0	V
V_C	$I_{PP} = 2A, t_p = 8/20\mu s$			6.0	V
V_C	$I_{PP} = 10A, t_p = 8/20\mu s$			9.0	V
C_{ESD}	$V_R = 3.3V, f = 1MHz$		1.5	2.0	pF
C_{Δ}	$V_R = 0V \sim 3.3V, f = 1MHz$		1.5		pF

8/20 μ s Pulse Waveform

Clamping Voltage V_C vs. Current I_{PP}

Insertion Loss S21

Normalized Capacitance vs. Voltage

**ESD Clamping of I/O to GND
(+8kV Contact per IEC 61000-4-2)**

**ESD Clamping of I/O to GND
(-8kV Contact per IEC 61000-4-2)**


Package Outline


- DFN1006-2L package
- 2 leads, very small package
- MSL-1




Package Dimensions (Controlling dimensions are in millimeters)

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Minimum	Maximum	Minimum	Maximum
A	0.450	0.550	0.017	0.022
A1	0.000	0.050	0.000	0.002
D	0.950	1.050	0.037	0.041
E	0.550	0.650	0.022	0.026
b	0.200	0.300	0.008	0.012
e	0.650 BSC		0.026 BSC	
L	0.450	0.550	0.018	0.022

Tape and Reel Specification



Symbol	W	A0	B0	K0	E	F	P	P0	P2	T
Dimensions (mm)	8.00±0.1	0.7±0.05	1.15±0.05	0.55±0.05	1.75±0.1	3.5±0.05	2.0±0.1	4.0±0.1	2.0±0.05	0.2±0.05



Symbol	Reel Size	M	N	W	W1	H	S	K	R
Dimensions (mm)	Φ178	178.0±1.0	60.0±1.0	11.5±0.5	9.0±0.5	13.0±0.5	2.0±0.1	11.0±0.2	1.0±0.05


Ordering Information

Part Number	Working Voltage	Quantity Per Reel	Reel Size
TS0301VBX	3.3V	10,000	7 Inch

Marking Codes



Or



Note:

(1) “PB” is part number, fixed

Note:

(1) “1P” is part number, fixed