




RIGHT BENDING FOOT



KW 2 - 2 - 02 CR - 30 - 3

Small belt certification



W2=Silver contact

1=0.05A
2=1.0A
3=3.0A

00=No pressure handle
01=Plastic pressure handle
02=Hardware pressing handle

1=Red button
2=White button
3=Black button
5=Grey button

N=Soldering foot
P=DIP
L=long foot
CR=Right bending foot
CL=Left bending foot



CIRCUIT DIAGRAM

7	PRESSING HANDLE	1	STAINLESS STEEL	
6	TERMINAL	3	C2680	Ag plating
5	CONTACT	1	SILVER-NICKEL ALLOY	
4	STEM	1	PBT LOCKING FUEL	
3	CONTACT	1	C17200	
2	COVER	1	PBT LOCKING FUEL	
1	BASE	1	PBT LOCKING FUEL	
NO.	PART NAME	NUMBER	MATERIAL	REMARK



RoHS
Compliant
2002/95/EC



Rating	1A 125VAC	Electrical Life	6,000 cycles
Contact Resistance	100mΩ Max	Mechanical Life	1,000,000 cycles
Insulation Resistance	>100MΩ DC500V	Ambient Temper. Used	-25℃ to +85℃
Withstand Voltage	AC500V 1min.	Ambient Humidity Used	≤85% at +40℃
Soldering Temper.	235±5℃ 5s	Operating Force	30±15gf max

SCALE: 1:1	UNIT: mm	Title: Micro Switch			
SIZE: A4		Molde Code: KW2-2-02CR-30-3			
Unless otherwise General Tolerance: X. ±0.30 X.x ±0.20 X.xx ±0.15 X.xxx ±0.10 Angles ±3°		DRAWN	CHECKED	APPROVED	DATE
		Xia	Chen	Chen	2025.04.17
		REV: A0	SHEET: 1/1		

品赞科技®
b-Switch