

RoHS Compliant


Process Capable

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		






SLIDE SHELL LOCK




NOTES:
1.MATERIAL:
- 1.1. HOUSING: THERMOPLASTIC,UL94V-0;
- 1.2. TERMINAL: COPPER ALLOY.;
- 1.3. SHELL: STAINLESS STEEL.


2.FINISHED:
- 2.1. TERMINAL: Ni PLATED UNDER,Au PLATED ON CONTACT AREA,G/F PLATED ON SOLDER TAIL;

3.ELECTRICAL CHARACTERISTICS
- 3.1. CURRENT RATING : 0.5A MAX.
- 3.2. IDIELECTRIC WITHSTANDING VOLTAGE: 500V AC R.M.S. FOR 1 MINUTE.
- 3.3. INSULATION RESISTANCE : 100MΩ MIN.AT 500V DC.
- 3.4. CONTACT RESISTANCE : 50mΩ MAX. SWITCH RESISTANCE : 100mΩ MAX.
- 3.5. OPERATION TEMPERATURE RANGE:-30°C~+85°C



PAD AREA
RECOMMENDED PCB LAYOUT(TOLERANCE ±0.05)





X. ±0.50	X.° ± 2°	UNITS mm
.X ±0.30	.X° ± 1°	MAT'L
.XX ±0.10	.XX° ± 0.5°	
.XXX ± 0.05		FINISH
		Q'TY

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF SHENZHEN CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF SHENZHEN CHUANGYUE TECHNOLOGY CO., LTD

广东创粤科技有限公司

TITLE: TF 掀盖H1.8卡座

TF-H1.8-30215

DWG NO.:

CHKD:

DR:

SCALE	SHEET	REV.
1/1	1/1	A1