PINTECH 品致®

Differential Probe DP-210



Characteristic

- 2% accuracy.
- Adaptor power supply.
- Standard BNC interface, compatible with any brand's oscilloscope.

Model	DP-210
Bandwidth(-3dB)	DC-100MHz
Attenuation Ratio	50X,500X
Accuracy	±2%
Rise Time	≥3.5ns
Input differential Vp-p	50X:260V; 500X:2600V
Input differential V AC RMS	919V
Input differential V DC	50X:130V; 500X:1300V
Common mode voltage(rms)	919V
Input Impedance	5MΩ//2pF(Single-ended); 10MΩ//1pF(Both ends)
Noise RMS	50X:≤200mV rms; 500X:≤400mV rms
5MHz Bandwidth limited	Switchable:Full/5MHz
Oscilloscope input impedance	1MΩ
Power adaptor	External 5V DC power supply
CMRR(Tyical)	60Hz:>80dB; 100Hz:>60dB; 1MHz:>50dB
Temperature	0~50°C
Humidity	10~85%RH
Weight	285g
Dimension(L*W*H)	175×68×28mm

● ACCESSORIES


Adapter


USB


BP-256N


BP-276N


BP-366A


BP-286N


Plug Adaptor

GUANGZHOU PINTECH CO.,LTD
Web:www.pintech.com.cn
Tel:020-82510899
E-mail:sales@pintech.com.cn

Main Products

Optical Isolated Voltage Probe, Differential probe, Oscilloscope probe, High voltage probe, High frequency current probe, Current probe, Digital high voltage meter, High voltage amplifier, Power amplifier, ESD generator, Function generator, Oscilloscope, Spectrum analyzer, multimeter, High voltage power supply, AC power supply, DC power supply and Power equipment instrument.