










- MECHANICAL :
1. HOUSING MATERIAL: PBT, PA46, BLACK
  2. INSERT MATERIAL: PBT, PA46, BLACK
  3. TERMINAL: PHOSPHOR BRONZE  $\phi 0.46\text{MM.G/FU}$  GOLD PLATING
  4. SHIELD: BRASS  $T=0.2\text{mm}$  PLATED NICKEL 30u" Min
  5. OPERATING LIFE: 750 CYCLES MIN
  6. MATING/UNMATING FORCE: 30N/3.06KGf MAX
  1. VOLTAGE RATING: 125 VAC RMS
  2. CURRENT RATING: 1.5 AMP
  3. CONTACT RESISTANCE: 30m MAX.
  4. INSULATION RESISTANCE: 500 MEGA OHMS MIN. INITIAL
  5. DIELECTRIC STRENGTH: 1000VAC RMS 50HZ OR 60HZ, 1MIN.
  1. STORAGE:  $-40^{\circ}\text{C}$  TO  $+85^{\circ}\text{C}$
  2. OPERATION:  $-40^{\circ}\text{C}$  TO  $+85^{\circ}\text{C}$
  3. The mark with "\*" is key inspection dimension for QC

#### LED Specification

| Standard LED Color | LED Wavelength | Foward(A) | Foward(V)  |
|--------------------|----------------|-----------|------------|
| Yellow             | 568nm          | 20mA      | 1.85-2.45V |
| Green              | 585nm          | 20mA      | 1.7-2.2V   |



|           |                        |                         |                  |                                                                                       |                                                                                                                                                |                 |             |     |
|-----------|------------------------|-------------------------|------------------|---------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|-----------------|-------------|-----|
|           |                        | GENERAL TOLERANCE       | 制图<br>DRAWING    | 04                                                                                    |  深圳市华灿天禄电子有限公司<br>ShenzhenhuacantianluELECTRONICS CO.,LTD |                 |             |     |
|           |                        | DIM TOL                 | 审核<br>CHECK      |                                                                                       |                                                                                                                                                |                 |             |     |
|           |                        | X.X $\pm 0.30$          | 批准<br>APPROVAL   |                                                                                       | 产品名称<br>TITLE                                                                                                                                  | 网络插座            | 版本<br>REV.  | A   |
| 1         | 初版发行                   | X.XX $\pm 0.20$         | 比例<br>SCALE      |                                                                                       | 产品料号<br>PART NO.                                                                                                                               | HC-RJ45-059-2-2 | 单位<br>UNITS | mm  |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE       | 投影<br>Projection |  | 材料<br>MATERIAL                                                                                                                                 |                 | 页次<br>SHEET | 1/1 |
|           |                        | X.XXX $\pm 0.10$        |                  |                                                                                       |                                                                                                                                                |                 |             |     |
|           |                        | Angle $\pm 3.0^{\circ}$ |                  |                                                                                       |                                                                                                                                                |                 |             |     |