

RoHS Compliant 2011/65/EU


Process Capable


Compliant Halogen Free

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN










[Schematic]



[P.C.B.LAYOUT]

NOTES:

1.Specification:

1>.Operation force: 1000gf Max.

2>.Operation Temperature: -30℃ to +85℃.

3>.Storage Temperature: -40℃ to +85℃.

4>.Mechanical Life: 1000 cycles operations.

5>.Resistance to Soldering: 260±5℃ for 3-5 Seconds.

2.PLATING:

1>.GOLD flash 1u"(min) SOLDERTAIL,

3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

1>.Non-switch Rating:100mA at 50V DC.

2>.Switching Rating: 25mA at 24V DC.

3>.Contact Resistance: Inital 50mΩ Max.

Contact Resistance: After life 100mΩ Max.

4>.Insulation Resistance:100MΩ Min at 100VDC.

5>.Dielectric Strength: 300V AC for 60seconds.

6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DSHP XX T S G E R

- R (包装方式:T=Tub R=Reel)
- E (电镀层:E=接触位3u"/焊接位1-2u")
- G (电镀层:G=端子内外电镀全金)
- S (端脚型:S=贴片 / D=插件 / J型)
- T (L=高柄 / S=低柄 / T=低柄贴胶)
- XX (开关位数: 02位-----10位)

5.PACKING: 2000pcs/Reel/Box.

TOLERANCE	
>0±0.05	>0°±0.5°
>1±0.10	>5°±1.0°
>10±0.30	
UNITS	mm
MATERILA	— — —
FINISH	— — —

深圳聚兴泰电子科技有限公司
Shenzhen Juxingtai Electronic Technology Co., Ltd

PART NO. DSHP10TSGER	TITLE:PRODUCT Family DSHP Series Pitch 1.27mm
DESIGN: Ethan	MANUFACTURE DWG
CHED: Olvia	SCALE N:A / SHEET 1/1
APPD: Ava	

JXTCONN