61.011.11 ✔ ACTIVE



TE Internal #: 61-0011-011-000

Standard Circular Connectors, Signal, Brass, Size 23, 0° Alignment Keyed, Metal, Pin

View on TE.com >

Connectors > Circular Connectors > Standard Circular Connectors



Sealable: **No**

Contact Current Rating (Max): **20 A**

Circuit Application: **Signal**

Shell Base Material: **Brass**

Circular Connector Shell Size: **23**

Features

Product Type Features

Sealable	No
Shell Type	Metal

Body Features

Shell Base Material	Brass

Contact Features

Contact Current Rating (Max)	20 A
Circular Connector Contact Type	Pin

Termination Features

Termination Method to Wire & Cable	Solder

Housing Features

Circular Connector Shell Size	23
Alignment Keyed	0°

Operation/Application

Durability Rating	500 Cycles

Circuit Application	Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) SVHC > Threshold: Pb (3.5% in Component part) **Article Safe Usage Statements:** Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 60-0014-011-000
CONTACT SOCKET 2 MM

Customers Also Bought



TE Part #1-175216-2
DYNAMIC D-3 REC CONT. S AU 0.38 L /P



TE Part #5747971-3
MOUNTING SCREW, ZN PLTD



TE Part #9-1423364-6
W57-XB1A7A10-5=CKTBKR,THERM, PB,SCW/QC



TE Part #5-1423364-5
W57-XB6A99C10-7=CKTBKR,THERM, PB,QC.250



TE Part #2141230-1
3POS,PIN DIA 8.0,PIN HSG,ASSY,SLD



TE Part #60-0012-011-000
CONTACT SOCKET 2 MM



TE Part #60-0014-011-000
CONTACT SOCKET 2 MM



TE Part #61-0006-011-000
CONTACT PIN 1 MM



TE Part #ASA021N00100235000
623 PLUG



TE Part #2-1103101-3
HN.D.7.BU.C. 250 V

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_61-0011-011-000_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_61-0011-011-000_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_61-0011-011-000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

61-0011-011-000

English