

1.Features

The RCLAMP0521P is a bi-directional TVS diode, utilizing leading monolithic silicon technology to provide fast response time and low ESD clamping voltage, making this device an ideal solution for protecting voltage sensitive high-speed data lines.

3.Features

- Ultra low capacitance: 0.3pF typical
- Ultra low leakage: nA level
- Operating voltage: 5V
- Low clamping voltage
- 2-pin leadless package
- RoHS Compliant

4.Applications


- Cellular Handsets and Accessories
- Display Ports
- MDDI Ports
- USB Ports
- Digital Video Interface (DVI)
- PCI Express and Serial SATA Ports

2.Mechanical Characteristics

- Case Material: “Green” Molding Compound.
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminal Connections: See Diagram Below
- Marking Information: See Below

- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
 - Air discharge: ±25kV
 - Contact discharge: ±22kV
 - IEC61000-4-5 (Lightning) 4A (8/20µs)

5.Pinning Information



DFN1006-2



6. Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Units
Peak Pulse Power (8/20 μs)	P_{PK}	100	W
Peak Pulse Current (8/20 μs)	I_{PP}	4	A
ESD per IEC 61000-4-2(Air)	V_{ESD}	± 25	kV
ESD per IEC 61000-4-2(Contact)		± 22	kV
Junction Temperature Range	T_J	-55 to 125	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55 to 150	$^\circ\text{C}$

7. Electrical Characteristics ($T_A=25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Reverse Working Voltage	V_{RWM}				5	V
Breakdown Voltage	V_{BR}	$I_T=1\text{mA}$	6.5		9.5	V
Reverse Leakage Current	I_R	$V_{RWM}=5\text{V}$			0.2	μA
Clamping Voltage	V_C	$I_{PP}=1\text{A}$ (8 x 20 μs pulse)			12	V
		$I_{PP}=4\text{A}$ (8 x 20 μs pulse)			25	V
Junction Capacitance	C_J	$V_R=0\text{V}$, $f=1\text{MHz}$		0.3	0.5	pF




8. Typical Characteristic

<p>Figure 1: Junction Capacitance vs. Reverse Voltage</p>	<p>Figure 2: Peak Pulse Power vs. Pulse Time</p>
<p>Figure 3: Clamping Voltage vs. Peak Pulse Current</p>	<p>Figure 4: Power Derating Curve</p>
<p>Figure 5: 8 X 20μs Pulse Waveform</p>	<p>Figure 6: ESD Clamping Voltage 8 kV Contact per IEC61000-4-2</p>



9.DFN1006-2L Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	b	c	D	e	E	L	L1	h
Min	0.45	0.00	0.45	0.12	0.95	0.65	0.55	0.20	0.05	0.07
Max	0.55	0.05	0.55	0.18	1.05	BSC	0.65	0.30	REF	0.17



10. Ordering Information



Order Code	Package	Base QTY	Delivery Mode
UMW RCLAMP0521P	DFN1006-2	10000	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.