




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **250 VAC**

Contact Retention Within Housing: **With**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Mating Pin Diameter	2.13 mm[.084 in]
Wire Contact Termination Area Plating Material Finish	Matte
Contact Orientation	Straight
Contact Type	Pin
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Brass
Contact Current Rating (Max)	15 A

Termination Features



Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
Contact Retention Type Within Housing	Locking Lance

Dimensions

Compatible Insulation Diameter Range	2.92 mm[.115 in]
Wire Size	.8 – 1.31 mm²

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 91504-1 CCII CMNL MNL PIN SKT 20-14 ASSY	 TE Part # 455830-1 INSERTION TOOL	 TE Part # 1-171196-0 6 POS MATE-N-LOK S	 TE Part # 1-480274-0 09P CMNL PLUG HSG P/M NATL
 TE Part # 1-480284-0 08P CMNL CAP HSG M/M NATL	 TE Part # 1-480438-0 16P CMNL PLUG HSG M/M NATL	 TE Part # 1-480683-0 02P CMNL PLUG HSG F/H NATL	 TE Part # 1-480277-0 09P CMNL CAP HSG P/M NATL
 TE Part # 1-480304-0 03P CMNL PLUG HSG P/M NATL	 TE Part # 1-480722-0 04P CMNL PLUG HSG W/LCK NATL	 TE Part # 1-480276-0 06P CMNL CAP HSG P/M NATL	 TE Part # 1-480285-0 10P CMNL PLUG HSG M/M NATL
 TE Part # 1-480439-0 16P CMNL CAP HSG M/M NATL	 TE Part # 1-480393-1 02P CMNL PLUG HSG F/H BLK	 TE Part # 1-480345-0 08P CMNL CAP HSG F/H NATL	 TE Part # 1-480340-0 06P CMNL CAP HSG F/H NATL



TE Part # 1-480278-0
12P CMNL CAP HSG P/M NATL

TE Part # 1-480425-0
04P CMNL PLUG HSG P/M NATL

TE Part # 1-480324-0
15P CMNL CAP HSG P/M NATL

TE Part # 1-480721-0
03P CMNL PLUG HSG W/LOK NATL

Also in the Series | Commercial MATE-N-LOK

Connector Caps & Covers(2)

Connector Contacts(150)

Connector Seals & Cavity Plugs(1)

Crimp Wire Pins, Tabs & Ferrules(2)

Insertion & Extraction Tools(3)

Rectangular Connector Housings(9)

Rectangular Power Connectors(166)

Standard Circular Connectors(2)

Standard Rectangular Connectors(7)

Customers Also Bought


TE Part #5226990-6
PCB-BNC RT ANGLE JACK W/O POST

TE Part #1609112-3
10CE1 M0=F7804

TE Part #1-480274-0
09P CMNL PLUG HSG P/M NATL

TE Part #770075-1
04P .093 COMM P&S RECPT HSG





TE Part #480115-3
FF 250 REC HSG 2P NYLON BLACK



TE Part #770070-1
03P .093 COMM P&S RECPT HSG



TE Part #770074-1
03P .093 COMM P&S PLUG HSG



TE Part #1-480275-0
12P CMNL PLUG HSG P/M NATL



TE Part #CTJ-3A-04-4021
RAIL ASSY

Documents

Product Drawings

MNL PIN PTPBR

English

CAD Files

Customer View Model

ENG_CVM_350639-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_350639-1_F.3d_stp.zip

English

Customer View Model

ENG_CVM_350639-1_F.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

350639-1

Pin Contact, Tin, 250 VAC, Locking Lance Contact Retention, 18 – 16 AWG Wire Size, .
8 – 1.31 mm² Wire Size, Crimp, Brass, Power, Commercial MATE-N-LOK



English