







Poles	02	03	04	05	06	07	08	09	10	11	12
Dim L	25.40	38.10	50.80	63.50	76.20	88.90	101.60	114.30	127.0	139.70	152.40
Dim B	12.70	25.40	38.10	50.80	63.50	76.20	88.90	101.60	114.30	127.0	139.70
TOL	±0.15				±0.20				±0.30		

SIGN	DATE	DESCRIPTION	APPROVER
△			
△			

- Material:
- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
 - Item 2 Clamp : Steel stamping , Zinc plated
 - Item 3 Wire guard solder pin : Copper,Tin plated
 - Item 4 Terminal screw: Steel , Zinc plating"- "slot type

- Electrical cULus IEC
- Voltage rating : 300V 1000V
 - Current rating : 65A 76A
 - Wire range : 16.00mm
 - Solid wire (AWG) : 6-20
 - Stranded wire (AWG) : 6-20
 - Torque (LB-In.) : 19LB-In
 - Screw : M4.5
 - Wire strip length : 10-11mm
 - Withstanding voltage : 2.2KV 6KV
 - Operating temperature : -40°C+115°C
 - Soldering temperature : 250°C+10°C/5 Sec
 - Safety Approval : cULus

VP xx 85 x 8 xxxx G

- 02 2 CONTACTS 0: Black 0000 Standard @ Logo RoHS
- 03 3 CONTACTS 5: Green (RAL 6018/T) 000A Standard ANY Logo Pb<40,000ppm
- ... 6: Blue Any special item by customer request, please contact sales department.
- 12 12 CONTACTS 8: Grey (RAL 7035/D)

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		VP 12.70 Series (0.9×1.0) Contacts Pin Pitch 4.0mm ----Double parallel tail									
PART NO.		VPxx85x8xxxxG				DWG NO.		8VP0120			
APPROVED		CHECKED	DESIGNED	DRAWN		CUST NO.		Tolerance			
			Aaron 2009.11.16	Aaron 2009.11.16				UNIT: mm		X.	±0.50
								SCALE: NONE		X.X	±0.30
						SHEET: 01/01		REV: B		X.XX	±0.10
										X°	±1°