


REV.	ECN NO.	LOCAS.	DESCRIPTION	DATE	DESIGN
A			NEW DRAWING		



3D View

■ Specification



Voltage Rating : 50V AC/DC
Current Rating : 2A AC/DC
Withstanding Voltage : 500V AC /minute
Insulation Resistance : $\geq 100\text{M}\Omega$ min
Temperature Range : 40°C to $+105^{\circ}\text{C}$
Contact Resistance : $\leq 20\text{m}\Omega$
After Environmental Testing: $\leq 40\text{m}\Omega$
Suitable Wire/Cable:AWG #28 to #30,OD:0.8mm max

■ Ordering Information


- Category:W-Wafer
- Soldering PCB Angle:R-Right angle/ 90°
- Soldering method:S-SMD/SMT, Surface Mount Technology
- Number of rows&pins:XX
- Plug the pin & Special No.:Blank-Ordinary
- Material(Insulators):LP-LCP,UL94V-0
- Color:Blank-Natural;BK-Black
- Environmental protection Standard:Blank-Ordinary
- RoHS;HF-Halogen Free
- Material(Pin):PB-Phosphor Bronze
- Plating :SN-Bright Tin Plated;SM-Matte Tin Plated;AU-Gold flash;AU3-Gold 3U"
- Package:Blank-Tape&Reel,SPQ:4K/reel preferred

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
04	3.60	6.60	5.04	08	8.40	11.40	9.84
05	4.80	7.80	6.24	09	9.60	12.60	11.04
06	6.00	9.00	7.44	10	10.80	13.80	12.24
07	7.20	10.20	8.64				


		Xiping Huang			广东国连电子有限公司	
		Ke Tian			GUANGDONG GUOLIAN ELECTRONICS CO.,LTD	
D:	Youquan Xu			TITLE:		
	TOL	DIM	TOL	1.2卧贴 4-5P		
	±0.25	X°	±3.0°	PART NO.		
	±0.20	X.X°		A1201AWR-NP-***		
	±0.15	X.XX°		REV. A		
		X.XXX		SCALE:	N/A	UNIT:
						mm
						SHEET:
						1/1
						



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05



6P With Sticking Point
Scale 1:1



7~10P With Sticking Point
Scale 1:1
Furthermore be able to 11P,12P