

STRAIGHT PLUG CLAMP TYPE


CABLE 5/50 S - PACK 100

R141.007.161

Series : **BNC-COM**







All dimensions are in mm.

COMPONENTS	MATERIALS	PLATINGS (µm)
BODY	**BRASS**	**NICKEL 2**
CENTER CONTACT	**BRASS**	**GOLD 0.2 OVER NICKEL 2**
OUTER CONTACT	-	-
INSULATOR	**WHITE POLYPROPYLENE**	
GASKET	**SILICONE RUBBER**	
OTHERS PARTS	**BRASS**	**NICKEL 2**
-	-	-
-	-	-

Issue : 0309 E

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIALL®

STRAIGHT PLUG CLAMP TYPE

CABLE 5/50 S - PACK 100

R141.007.161

Series : **BNC-COM**

PACKAGING

Standard	Unit	Other
100	**'W' option**	**Contact us**

ELECTRICAL CHARACTERISTICS

Impedance		**50**	Ω
Frequency		**0-1.5**	GHz
VSWR	**NA +**	**0.000**	x F(GHz) Maxi
Insertion loss		**0.115**	√F(GHz) dB Maxi
RF leakage	**- (**	**57**	- F(GHz)) dB Maxi
Voltage rating		**500**	Veff Maxi
Dielectric withstanding voltage		**1500**	Veff mini
Insulation resistance		**5000**	MΩ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force – Mating end	**NA**	N mini
Axial force – Opposite end	**NA**	N mini
Torque	**NA**	N.cm mini

Recommended torque

Mating	**NA**	N.cm
Panel nut	**NA**	N.cm
Clamp nut	**150**	N.cm
A/F clamp nut	**9.500**	mm

Mating life	**100**	Cycles mini
Weight	**12.500**	g

ENVIRONMENTAL

Operating temperature	**-35/+70**	° C
Hermetic seal	**NA**	Atm.cm3/s
Panel leakage	**NA**	

SPECIFICATION

CABLE ASSEMBLY

Stripping	a	b	c	d	e	f
mm	2.50	7.00	0.00	0.00	3.00	0.00

Assembly instruction : **Clamp 03**

Recommended cable(s)
RG 58
KX 15
RG 141

Cable retention

- pull off	**180**	N mini
- torque	**NA**	N.cm

TOOLING

Part Number	Description	Hexagon
.	.	.

OTHERS CHARACTERISTICS

-

Issue : 0309 E

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

RADIALL®