

Digital Attenuator Die, 6-Bit, Parallel Control

0.1 - 30 GHz, 31.5 dB Attenuation Range



MAAD-011036-DIE

Rev. V3

Features

- 6-Bit Digital Attenuator, 0.5 dB LSB
- 31.5 dB Attenuation Range
- Wide Frequency Range: 0.1 - 30 GHz
- Parallel Control:
 - Complementary Controls (per bit)
- Attenuation Accuracy: typ.
+/- (0.5 + 5% of Attenuation Setting) dB
- Die Size: 2.73 x 1.38 x 0.10 mm

Applications


- Test Equipment (instrumentation)
- Communications (commercial and military) :
 - Cellular Infrastructure
 - Radars
 - Radios (MMW)
- General Purpose

Description

The MAAD-011036-DIE is a 6-bit, 0.5 dB step GaAs pHEMT MMIC digital attenuator covering a large frequency range from 0.1 to 30 GHz with excellent insertion loss and attenuation accuracy.

This device is ideally suited for use where high accuracy, very low power consumption, and low intermodulation products are required.

Functional Schematic



Pin Configuration

Pin #	Function	Description
1, 3, 4, 6	GND	Ground ¹
2	RF IN	Input RF
5	RF OUT	Output RF
7, 16, 18	NC	No Connection
8	Vcontrol_B6	16 dB BIT Vcontrol_B6
9	Vcontrol_A6	16 dB BIT Vcontrol_A6
10	Vcontrol_B5	8 dB BIT Vcontrol_B5
11	Vcontrol_A5	8 dB BIT Vcontrol_A5
12	Vcontrol_B4	4 dB BIT Vcontrol_B4
13	Vcontrol_A4	4 dB BIT Vcontrol_A4
14	Vcontrol_B3	2 dB BIT Vcontrol_B3
15	Vcontrol_A3	2 dB BIT Vcontrol_A3
17	Vcontrol_A2	BIT 1 dB Control_A2
19	Vcontrol_A1	BIT 0.5 dB Control_A1

1. All GND bondpads are connected to the secondary side of the die with substrate vias.

Ordering Information

Part Number	Package
MAAD-011036-DIE	Die in Gel Pack

* Restrictions on Hazardous Substances, compliant to current RoHS EU directive.

Digital Attenuator Die, 6-Bit, Parallel Control

0.1 - 30 GHz, 31.5 dB Attenuation Range



MAAD-011036-DIE

Rev. V3

Electrical Specifications^{2,3,4}

Freq. = 0.1 - 30 GHz, $T_A = 25^\circ\text{C}$, $Z_0 = 50\ \Omega$, $V_C = -5\ \text{V} / 0\ \text{V}$, $P_{IN} = 0\ \text{dBm}$

Parameter	Test Conditions	Units	Min.	Typ.	Max.
Reference Insertion Loss	0.1 - 18.0 GHz 18.0 - 26.5 GHz 26.5 - 30.0 GHz	dB	—	3.2 4.2 5.2	4.2 — 6.0
RMS Attenuation Error	0.1 - 30.0 GHz	dB	—	0.6	—
Attenuation Accuracy	Relative to Insertion Loss	$\pm (0.5 + 5\% \text{ of attenuation setting})\ \text{dB typ.}$			
Return Loss	All states (worst case)	dB	—	-12	—
Input P0.1dB	Reference State	dBm	—	21	—
IIP ₃	2-Tone, +10 dBm/tone, 1 MHz Spacing (Reference State)	dBm	—	43	—
T_{RISE} , T_{FALL}	10% to 90% RF, 90% to 10% RF	ns	—	15	—
V_C Current	Per bit	μA	—	0.5	—

2. Two bond-wires are recommended on pin 2 and 5 (1 mil diameter each). Keep these bonds to a minimum length (<130 μm).

3. Pins 1, 3, 17 and 19 must be RF/DC grounded thru bond wires (1 mil), one bond wire per GND pin.

4. RMS Calculation Discussion:

RMS Error is used directly to calculate system parameters. To derive RMS error, first normalize the attenuation for all conditions to the minimum loss condition. Next calculate an absolute error by taking the difference between the normalized measurement and the ideal attenuator loss for each state. By using this with the equation below, the RMS Error can be determined.

$$RMS\ ERROR, mean = \sqrt{\frac{1}{n} \sum (Er_i - Er_{Ave})^2}$$

Er_i = Ideal Error, Er_{Ave} = Normalized Error, n = number of attenuator bits (attenuator states = $2^{(n-1)}$)

Truth Table⁵

0.5 dB BIT		1 dB BIT		2 dB BIT		4 dB BIT		8 dB BIT		16 dB BIT		Attenuation (dB)
pin 19	pin 18	pin 17	pin 16	pin 15	pin 14	pin 13	pin 12	pin 11	pin 10	pin 9	Pin 8	
0	X	0	X	0	1	0	1	0	1	0	1	Reference IL
1	X	0	X	0	1	0	1	0	1	0	1	0.5
0	X	1	X	0	1	0	1	0	1	0	1	1
0	X	0	X	1	0	0	1	0	1	0	1	2
0	X	0	X	0	0	1	0	0	1	0	1	4
0	X	0	X	0	1	0	1	1	0	0	1	8
0	X	0	X	0	1	0	1	0	1	1	0	16
1	X	1	X	1	0	1	0	1	0	1	0	31.5

5. "0" = -5.3 V to -4.3 V, "1" = -0.2 V to 0 V, "X" = Don't Care.

Digital Attenuator Die, 6-Bit, Parallel Control

0.1 - 30 GHz, 31.5 dB Attenuation Range



MAAD-011036-DIE

Rev. V3

Absolute Maximum Ratings^{6,7}

Parameter	Absolute Maximum
Input Power	31 dBm
Control Voltage	$-5.5 \text{ V} \leq V_{\text{Controls}} \leq 0.5 \text{ V}$
Junction Temperature	+150°C
Operating Temperature	-40°C to +85°C
Storage Temperature	-65°C to +150°C


6. Exceeding any one or combination of these limits may cause permanent damage to this device.
7. MACOM does not recommend sustained operation near these survivability limits.

Mounting and Bonding Information

The DIE should be directly attached to the RF/DC ground plane; either with solder (AuSn) or a thin application of conductive epoxy. Avoid overflows.

Any connecting microstrip (50 Ω Transmission Line) substrate should be brought as close as possible to the die in order to minimize bond wire inductance. A typical spacing between die and microstrip substrate should be kept between 75 - 125 μm for best RF behavior. All bonds should be kept as short as possible. Use minimum ultrasonic energy for reliable wire bonds.

Outline Drawing



Bond Pad Dimensions (μm)

Pad	X	Y
1, 3, 4, 6 - 19	80	80
2, 5	80	192

Unless otherwise specified, all dimensions shown are μm with a tolerance of $\pm 5 \mu\text{m}$.

Die thickness is $100 \mu\text{m} \pm 10 \mu\text{m}$.

Bond pad/backside metallization is gold.

Die size reflects un-cut dimensions. Saw, or laser kerf reduces die size by $\sim 25 \mu\text{m}$ each dimension.


Digital Attenuator Die, 6-Bit, Parallel Control 0.1 - 30 GHz, 31.5 dB Attenuation Range




MAAD-011036-DIE

Rev. V3


Relative Attenuation (normalized S21) @ +25°C




S21 vs. Temperature (reference state)




S11 vs. Frequency (reference state)




S11 vs. Frequency (all states) @ +25°C




S22 vs. Frequency (reference state)



S22 vs. Frequency (all states) @ +25°C



RMS Error vs. Frequency (mean) @ +25°C




Digital Attenuator Die, 6-Bit, Parallel Control 0.1 - 30 GHz, 31.5 dB Attenuation Range




MAAD-011036-DIE

Rev. V3


BIT Error vs. Attenuation State, 0.1 - 18 GHz, @ +25°C




Input 0.1dB Compression vs. Frequency (reference state)




BIT Error vs. Attenuation State, 18 - 26.5 GHz, @ +25°C



Input IP3 vs. Frequency (reference state)



BIT Error vs. Attenuation State, 26.5 - 30 GHz, @ +25°C



Digital Attenuator Die, 6-Bit, Parallel Control

0.1 - 30 GHz, 31.5 dB Attenuation Range



MAAD-011036-DIE

Rev. V3

MACOM Technology Solutions Inc. ("MACOM"). All rights reserved.

These materials are provided in connection with MACOM's products as a service to its customers and may be used for informational purposes only. Except as provided in its Terms and Conditions of Sale or any separate agreement, MACOM assumes no liability or responsibility whatsoever, including for (i) errors or omissions in these materials; (ii) failure to update these materials; or (iii) conflicts or incompatibilities arising from future changes to specifications and product descriptions, which MACOM may make at any time, without notice. These materials grant no license, express or implied, to any intellectual property rights.

THESE MATERIALS ARE PROVIDED "AS IS" WITH NO WARRANTY OR LIABILITY, EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING FITNESS FOR A PARTICULAR PURPOSE, MERCHANTABILITY, INFRINGEMENT OF INTELLECTUAL PROPERTY RIGHT, ACCURACY OR COMPLETENESS, OR SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES WHICH MAY RESULT FROM USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.