





1. CURRENT RATING: 0.5A. MAX.
2. DIELECTRIC WITHSTANDING VOLTAGE:
500V AC R.M.S. FOR ONE MINUTE.
3. INSULATION RESISTANCE: 100MΩ MIN.AT 500V DC.
4. CONTACT RESISTANCE: 30mΩ MAX.
5. OPERATING TEMPERATURE: -25°C TO +85°C.
6. DURABILITY: 10000 CYCLES.
7. MATING FORCE: 4.5kgf MAX.
8. UNMATING FORCE: 1.0kgf MIN.



TOLERANCE:		DRAWN BY :	DATE :	PART NAME:	
X.X ±0.30		陈一鸣	2014-02-23	DP SMT 有弹带卡点 平口	
X.XX ±0.25					
X.XXX ±0.15		CHECKED BY:	DATE :	PART NO.	HYCW61-DP20-167B
X* ±2* X.X* ±0.5*		马跃	2014-02-23	MOLD NO.	
				APPROVED BY:	DATE :
UNIT: mm [inch]		邱敏	2014-02-23	SHEET NO.	1 OF 1
SCALE: 1:1	SIZE: A4				



TAPE & PACKAGE :

MATERIAL :

1. CARRIER TAPE : PS
2. COVER TAPE: PE
3. REEL : PS

QUANTITY:

1. 350 PCS/REEL
2. 10 REEL/CARTON: 3500PCS

DIMENSION :

- REEL SIZE :
DIA=380.0mm, W=32.0mm
- CARTON :
L=400mm, W=400mm, H=400mm



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.* ±2* X.X* ±0.5*	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	
 UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	
			SHEET NO.	1 OF 1