

Ordering Information:

C3030HF-2xXP - *** - ***
1 2 3


- 1.Part NO.
- 2.Material:
 (Blank): Nylon 66,UL94V-0(Black)
 GF15: Nylon 66+15% Glass Fiber,UL94V-0(Black)
 GWT: Nylon 66,UL94V-0(Black),
 IEC 60335-1,5th Edition
 Glow Wire Capable.
- 3.Color:
 (Blank): See Section 2 material
 BG:Beige WH:White
 RD:Red YL:Yellow
 GN:Green BL:Blue

SPECIFICATIONS:

- Current Rating: 8.5A AC,DC (MAX)
- Voltage Rating: 600V AC,DC
- Temperature Range: -40°C ~ +105°C
- Contact Resistance: 10mΩ Max
- Insulation Resistance: 1000MΩ Min
- Withstanding Voltage: 1500V AC/minute

Ordering Information & Dimensions

Part NO.	Dimensions(mm)	
	A	B
C3030HF-2x1P	--	3.85
C3030HF-2x2P	3.00	6.85
C3030HF-2x3P	6.00	9.85
C3030HF-2x4P	9.00	12.85
C3030HF-2x5P	12.00	15.85
C3030HF-2x6P	15.00	18.85
C3030HF-2x7P	18.00	21.85
C3030HF-2x8P	21.00	24.85
C3030HF-2x9P	24.00	27.85
C3030HF-2x10P	27.00	30.85
C3030HF-2x11P	30.00	33.85
C3030HF-2x12P	33.00	36.85



Unit	Scale	Sheet	TITLE
mm	2:1	1 of 2	3.00mm PITCH DUAL ROW HOUSING
DRWN	CHK'D	APPR	
Wenmin Luo	Diankui Wan	Jack Yin	
General Tolerances	THIRD ANGLE PROJECTION		DRAWING NO.
B1	JL-GC-ECN00480	2024.12.21	C3030HF-2xXP
A5	CHANGE THE DRAWING	2022.04.18	
REV	DESCRIPTION	DATE	
x.xx±0.25 x.xxx±0.20 x.xxxx±0.15 ANGLES ±1°			REV B1