


© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	11MAY2022	LL	DZ








W/ PICK AND PLACE TAPE
SCALE 4:1



W/ CAP
SCALE 4:1







NOTES
1. MATERIALS:
   PLASTICS: HIGH TEMPERATURE THERMOPLASTIC UL94V-0, COLOR: BLACK.
   SHELL: STAINLESS STEEL
   CONTACT: COPPER ALLOY.
   PICK AND PLACE TAPE: POLYIMIDE FILM.

2 FINISH:
   TERMINAL: CONTACT AREA: SELECTED GOLD PLATING, SEE TABLE.
   SOLDER AREA: MATTE TIN PLATING 100U" MIN.
   UNDER PLATING: NICKEL PLATING 50u" min OVER ALL.
   SHELL: UNDER PLATING: NICKEL PLATING 50u" min OVERALL.

3. HALOGEN REQUIREMENT MEET CODE 2: LOW BR/CL AS DEFINED IN TEC-138-72

4 TE CONNECTIVITY LOGO MARKED IN APPROXIMATE AREA SHOWN.

5 PART NUMBER AND DATE CODE MARKED IN APPROXIMATE AREA SHOWN.

Q'TY/CARTON	POCKET TAPE PITCH	Q'TY/REEL	CAP OPTION	2 CONTACT FINISH	DIM A	PART NUMBER
600	20	200	W/CAP	30u" GOLD	4.20MM	1-2360189-8
					3.00MM	1-2360189-7
					2.20MM	1-2360189-6
					1.50MM	1-2360189-5
				15u" GOLD	4.20MM	1-2360189-4
					3.00MM	1-2360189-3
					2.20MM	1-2360189-2
					1.50MM	1-2360189-1
			W/PICK AND PLACE TAPE	30u" GOLD	4.20MM	2360189-8
					3.00MM	2360189-7
					2.20MM	2360189-6
					1.50MM	2360189-5
				15u" GOLD	4.20MM	2360189-4
					3.00MM	2360189-3
					2.20MM	2360189-2
					1.50MM	2360189-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.30
2 PLC ±0.20
3 PLC ±0.10
4 PLC ±-
ANGLES ±2°

MATERIAL -
FINISH -

DWN LEO LI 05-AUG-2019
CHK DAVID ZHANG 05-AUG-2019
APVD DAVID ZHANG 05-AUG-2019
PRODUCT SPEC 108-60133
APPLICATION SPEC 114-60030
WEIGHT -

TE Connectivity


NAME MINI COOL EDGE IO INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD. 124P, SMT TYPE, 92OHM

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2360189	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 5 | REV A

© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




RECOMMENDED PCB LAYOUT
(GENERAL TOLERANCES: ±0.05)

SCALE 10:1


THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05-AUG-2019 LEO LI	TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.30 2 PLC ±0.20 3 PLC ±0.10 4 PLC ±- ANGLES ±2°	CHK 05-AUG-2019 DAVID ZHANG	NAME MINI COOL EDGE IO INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 92OHM
		APVD 05-AUG-2019 DAVID ZHANG	
		PRODUCT SPEC 108-60133	
		APPLICATION SPEC 114-60030	SIZE A1 · CAGE CODE 00779 · DRAWING NO C-2360189 · RESTRICTED TO -
MATERIAL - -	FINISH - -	WEIGHT -	CUSTOMER DRAWING · SCALE 5:1 · SHEET 2 OF 5 · REV A

© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



COMPONENTS KEEP OUT AREA
LIMITATION HEIGHT: 0mm
SCALE 6:1



COMPONENTS KEEP OUT AREA
SCALE 6:1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.30
2 PLC ±0.20
3 PLC ±0.10
4 PLC ±-
ANGLES ±2°

MATERIAL -
FINISH -

DWN	05-AUG-2019 LEO LI
CHK	05-AUG-2019 DAVID ZHANG
APVD	05-AUG-2019 DAVID ZHANG
PRODUCT SPEC	108-60133
APPLICATION SPEC	114-60030
WEIGHT	-

TE Connectivity

NAME: MINI COOL EDGE IO INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 920HM


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2360189	-


CUSTOMER DRAWING | SCALE 5:1 | SHEET 3 OF 5 | REV A


© 2019 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

RECOMMENDED AIC MATING CARD DIMENSIONS











THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO LI 05-AUG-2019	TE Connectivity
		CHK DAVID ZHANG 05-AUG-2019	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.30 2 PLC ±0.20 3 PLC ±0.10 4 PLC ±- ANGLES ±2°	APVD DAVID ZHANG 05-AUG-2019	NAME MINI COOL EDGE IO INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 92OHM
		PRODUCT SPEC 108-60133	
		APPLICATION SPEC 114-60030	SIZE A1 / CAGE CODE 00779 / DRAWING NO C-2360189 / RESTRICTED TO -
MATERIAL - -	FINISH - -	WEIGHT -	
		CUSTOMER DRAWING	SCALE 5:1 / SHEET 4 OF 5 / REV A

© 2019 TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-










FIGURE 1
DIRECTION OFF TOP OF REEL
FOR USER UNREELING
SHOWN AS -1 THRU -8
SCALE 2:1





DETAIL A
SCALE 5:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN LEO LI 05-AUG-2019	TE Connectivity
		CHK DAVID ZHANG 05-AUG-2019	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD DAVID ZHANG 05-AUG-2019	NAME MINI COOL EDGE IO INTEGRATED CONNECTOR, 0.6PITCH, VERTICAL STANDARD, 124P, SMT TYPE, 92OHM
	0 PLC ±- 1 PLC ±0.30 2 PLC ±0.20 3 PLC ±0.10 4 PLC ±- ANGLES ±2°	PRODUCT SPEC 108-60133	
		APPLICATION SPEC 114-60030	SIZE A1 / CAGE CODE 00779 / DRAWING NO C-2360189 / RESTRICTED TO -
MATERIAL - -	FINISH - -	WEIGHT -	CUSTOMER DRAWING / SCALE 5:1 / SHEET 5 OF 5 / REV A