


Common Mode Filter




- 1.High common mode impedance at high frequency Effects excellent noise suppression performance
- 2.100% Lead(Pb) & Halogen-Free and RoHS compliant.
- 3.Operating temperature-40~+125 C
- 4.Storage temperature range: -40 C to +125 C.

Part Number	Common mode Impedance (Ω)	Test Frequency (MHz)	DC Resistance (Ω) max.	Rated Current (mA)max.	Rated Volt. (Vdc)max.	Withstand Volt. (Vdc) max.	IR (Ω) min.
UTC2012C01 Q	800±25%	100	0.90	300	50	125	10M

MECHANICAL




SUGGESTED PAD LAYOUT




1. Unit: mm[inch]
2. Unless otherwise specified, all tolerances are ±0.20[.008]

TAPING AND PACKING




Direction of unreeling


SCHEMATICS



IMPEDEANCE FREQUENCY



Reel



Dimensions in mm

Quantity (pcs):
10000 PCS PER REEL
5 REELS PER CARTON
50000PCS PER CARTON