

Product data sheet

Specifications



Float switch, Pumptrol, open tank, NEMA 1, pedestal mounted, 2 NC DPST DB contacts

9036FG

Main

Range of product	Pumptrol
Product or component type	Float switch
Device application	Open tank pedestal style
Device short name	9036FG
Product specific application	Liquid level control
Electrical circuit type	Power circuit
Quantity per set	Set of 1
Type of packing	Individual

Complementary

Product destination	For open tank or sump
Device mounting	Pedestal
Cable entry number	2 22.35 mm cable entries with 0.84 in across flats conforming to UL 508
Contacts type and composition	2 NC, snap action, DPST-DB, Form YY
Controlled fluid	Fresh water at specific gravity of 0.85 in or higher Sea water at specific gravity of 0.85 in or higher Hydraulic oil at specific gravity of 0.85 in or higher Corrosive fluid at specific gravity of 0.85 in or higher
Motor power kW	1.5 kW (2 hp) at 115 V AC, 1 phase 2.2 kW (3 hp) at 115 V AC, 3 phases 2.2 kW (3 hp) at 230 V AC, 1 phase 3.7 kW (5 hp) at 230 V AC, 3 phases 0.75 kW (1 hp) at 460 V AC, 3 phases 0.75 kW (1 hp) at 475 V AC, 3 phases 0.18 kW (0.25 hp) at 32 V DC 0.37 kW (0.5 hp) at 115 V DC 0.37 kW (0.5 hp) at 230 V DC
Electrical connection	Screw-clamp terminals, clamping capacity: 10 AWG
Contact operation	Contacts close on liquid rise
Float movement	4...31 in adjustable
Float position	Any
Float rod angle	Vertical
Force down to trip	16 ozf
Force up to trip	16 ozf
Short-circuit protection	20 A cartridge fuse, type gG

Local signalling	Without
Materials in contact with fluid	Nylon Aluminium Zinc plated steel or equivalent Polystyrene
Enclosure material	Polypropylene or equivalent
Operating position	Vertical position only
Electrical durability	100 cycles, operating rate <60 cyc/mn
Mechanical durability	300 cycles
Terminal block type	4 terminals
Maximum operating rate	60 cyc/mn
[Ui] rated insulation voltage	575 V conforming to UL 508
Net weight	0.95 kg
Terminals description ISO n°1	Line-load-load-line
Factory modification	Without
Kit composition	Float switch Float Rod

Environment

Standards	CE UL 508
Ambient air temperature for operation	-30...93 °C
Ambient air temperature for storage	-30...93 °C
NEMA degree of protection	NEMA 1 conforming to UL 50
Product certifications	UL listed CSA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	50.0 cm
Package 1 Width	19.685 cm
Package 1 Length	127.0 cm
Package 1 Weight	952.544 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
---------------------------	---

Contractual warranty

Warranty18 months

Recommended replacement(s)