









3P貼Mylar示意图




2P貼Mylar示意图









10P-16P
SCALE 1:0.6




7P-9P
SCALE 1:0.6



5P-6P
SCALE 1:0.6





适用线路板(PCB Layout)

Part No	CKT	A	B	C	D
ZX-PA2.0-2PWT-BD	2	2.00	4.55	7.95	6.10
ZX-PA2.0-3PWT-BD	3	4.00	6.55	9.95	8.10
ZX-PA2.0-4PWT-BD	4	6.00	8.55	11.95	10.10
ZX-PA2.0-5PWT-BD	5	8.00	10.55	13.95	12.10
ZX-PA2.0-6PWT-BD	6	10.00	12.55	15.95	14.10
ZX-PA2.0-7PWT-BD	7	12.00	14.55	17.95	16.10
ZX-PA2.0-8PWT-BD	8	14.00	16.55	19.95	18.10
ZX-PA2.0-9PWT-BD	9	16.00	18.55	21.95	20.10
ZX-PA2.0-10PWT-BD	10	18.00	20.55	23.95	22.10
ZX-PA2.0-11PWT-BD	11	20.00	22.55	25.95	24.10
ZX-PA2.0-12PWT-BD	12	22.00	24.55	27.95	26.10
ZX-PA2.0-13PWT-BD	13	24.00	26.55	29.95	28.10
ZX-PA2.0-14PWT-BD	14	26.00	28.55	31.95	30.10
ZX-PA2.0-15PWT-BD	15	28.00	30.55	33.95	32.10
ZX-PA2.0-16PWT-BD	16	30.00	32.55	35.95	34.10

技术指标(Technical Index):

1.塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.

(The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)

2.工作温度(Temperature range):-25°C~+85°C.

3.额定电压(Rated voltage):250V, AC/DC.

4.额定电流:3.0A,AC/DC.

5.接触电阻(Contact resistance):≤20mΩ.

6.绝缘电阻(Insulation resistance):≥1000MΩ.

7.耐电压(Withstanding Voltage):800V AC/minute.

序号	品名	材质
①	2.0 R型卧式WTB胶壳 2.0 Pitch R/A Wire To Board Housing(H=5.7)	PA6T UL94V-0 米黄色 LCP UL94V-0 本色
②	2.0 R型卧式WTB端子 2.0 Pitch S/T Wire To Board Terminal(H=8.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating
③	2.0 R型卧式WTB焊片 2.0 Pitch R/A Wire To Board Fitting Nail(H=5.7)	铜合金/表面镀锡 Copper Alloy/ Tin Plating

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE

GENERL TOLERANCE	
X.:±0.50	±1°
X.X:±0.20	
X.XX:±0.10	

制图 DRAWING	ROSE		
审核 CHECK	LEO		
核准 APPROVAL	JOHN		
单位 UNITS	MM	比例 SCALE	1:1

料号 PART NO.	ZX-PA2.0-NPWT-BD	版本 REV.	A
品名 TITLE	2.00 Pitch R型卧式WTB	页次 SHEET	1/1
客户料号 CUTM.NO.			

兆星精密电子（深圳）有限公司
ShenZhen ZhaoXing Precision electronics Co., Ltd.