




REV.	ECN NO.	REVISED	DATE

NOTE:

- 1.MATERIAL:
a.HOUSING:PP BLACK
b.SPRING:SPRING WIRE
(SURFACE PLATING: Ni-PLATING)
SEE ORDERING INFORMATION
- 2.ELECTRIC:
a.DIELECTRIC VOLTAGE: 270V AC ONE MINUTE
b.OPERATING TEMPERATURE: -10° C~ +80° C



ORDERING INFORMATION
BH-AAA-B1AJ011-150

电池盒
电池型号
SMT 180° TYPE

线长mm
PLATING:
A-Au1U"
J-Ni-PLATING
K-Sn-PLATING

MATERIAL:
1A-PP BLACK
1B-PA66 BLACK
2A-PPA BROWN
2B-PPA BLACK
3A-PPS BROWN
3B-PPS BLACK
4A-LCP WHITE
4B-LCP BLACK



UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com	
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND WangHeng	DATE 2024-11-19
WEIGHT:		CHKD ZhouRuicai	DATE 2024-11-19
SHEET 1 OF 1		APVD XueShunYong	DATE 2024-11-19
SCALE:		SIZE: A4	VIEW:
UNIT: mm		REV.: A/1	OBJECT: MY
TITLE: 电池盒BH-AAA-4J 新 (26#线长150mm剥皮上锡3mm)		PART NO.: BH-AAA-B1AJ011-150	
DRAW NO.:WD-CP-0124			

2	SPRING	4	SPRING WIRE	Ni-Plating
1	HOUSING	1	PP	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR