





DIMENSION		Poles	Tolerance
Dim L	N×9.52	2p-6p	±0.15
Dim A	(N-1)×9.52	7p-12p	±0.25
		13p-16p	±0.35

N=Number of contacts



SIGN	DATE	DESCRIPTION	APPROVER
△	08/04'10	Clamp is chnged	Aaron
△	01/19'10	Add is cULus	Aaron
△	04/02'11	Add is spec.	Runner

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ㉓ Terminal housing : Thermoplastic (UL94V-0)
- Item ㉔ Clamp : Brass, Ni plated
- Item ㉕ Wire guard solder pin : Copper , Tin plated (Side Contacts)
- Item ㉖ Terminal screw: Steel Zinc plating "--" slot type
- Item ㉗ Wire guard solder pin : Copper , Tin plated (Center Contacts)

Electrical:

- Voltage rating: 600 V
- Current rating: 30 A
- Wire range:
- Solid wire(AWG): 10-24
- Stranded wire(AWG): 10-24
- Torque: 5.5 Lb-In
- Screw: M3.5
- Wire strip length: 7-8 mm
- Withstanding Voltage: 2.2KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec

△ Safety Approval:

KO xx 21 x 1 xxxx G

			RoHS Pb<40,000ppm
No. of poles end	0 Black (RAL9005)	0000 Standard @ Logo	
stackable design	2 Red (RAL3001/D)	000A Standard ANY Logo	
02 2 CONTACTS	3 Orange(RAL2011/P)	Any special item by	
03 3 CONTACTS	4 Yellow(RAL1018/A)	customer request,	
...	5 Green(RAL6018/T)	please contact sales	
16 16 CONTACTS	6 Blue (RAL5015/A)	department.	
	8 Grey(RAL7035/D)		

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		KO 9.52 Series 2P-16P (Double row Pin)				
PART NO.	K0xx21x1xxxxG			DWG NO.	8K00001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Runner 2011.04.02	Aaron 2009.10.20		Tolerance	
					UNIT: mm	X. ±0.50
					SCALE: NONE	X.X ±0.30
				SHEET: 01/01	RFV: F	X.XX ±0.10
						X° ±1°