DMC-MD 26 A ✔ ACTIVE



DEUTSCH


TE Internal #: ZPF000000000104586

Standard Rectangular Connectors, Housing, Receptacle, Mating Alignment, Keyed Mating Alignment Type, Mating Retention, Shielded, Normal, 1 Position

View on TE.com >

Connectors > Rectangular Connectors > Standard Rectangular Connectors > Rectangular Connector Receptacle Extenders, Tool-less Assembly




Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Mating Alignment: **With**

Mating Alignment Type: **Keyed**

Mating Retention: **With**

All Rectangular Connector Receptacle Extenders, Tool-less Assembly (26)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Insertion Force Type	Normal
Sealable	Yes

Configuration Features

Contacts Preloaded	No
Number of Positions	1
Number of Rows	1

Electrical Characteristics

Operating Voltage	125 VAC

Body Features

Connector & Keying Code	A

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Locking Latch
Connector Mounting Type	Panel Mount

Housing Features

Housing Material	Composite

Usage Conditions

Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Operation/Application

Shielded	Yes
Circuit Application	Power & Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked.Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for

substances in articles'(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # ZPF000000000100828
DMC-MD 20 A

Customers Also Bought



TE Part #DT04-6P-CE01
REC, 6P, GRY, E, CAP



TE Part #D369-P99-NS1
369 9 WAY PLUG, CRIMP, SKT



TE Part #ZPF000000000007566
983-0SE 14-07 PN-L



TE Part #ZPF000000000034473
983-0YE 08-98 PN



TE Part #2226455-1
SOCKET INSERT, 16-02 CABLE APPLIED

TE Part #YWM16BF06-05SA994L
PLUG ASSY.

TE Part #33526M11-08PC
RECP ASSY

TE Part #AAC0609-00
PC4240035-1597PN-1-B



TE Part #5510050014
PD-CAP-3/8-0-CS-34034

TE Part #2592494001
SRFR-10/6.5-8-CS-34034

Documents

Product Drawings

DMC-MD 26 A

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_ZPF000000000104586_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_ZPF000000000104586_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_ZPF000000000104586_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

DMC-M Series Single Module EN4165

English