



P. C. B Layout

技术要求:
Technical requirement

- 一. 电气性能:
electrical performance
1-1. 额定电流: 3A AC DC.
rated current: 3A AC DC.
1-2. 接触电阻: $\leq 20m\Omega$
Contact resistance: $\leq 20m\Omega$
1-3. 绝缘电阻: $\geq 1000M\Omega$
Insulation resistance: $\geq 1000M\Omega$
1-4. 耐 压: 550V AC/Minute
withstand voltage: 550V AC/Minute
- 二. 物理特性:
Physical characteristics
2-1.: 环境温度-55℃~105℃
environmental temperature:-55℃~105℃
2-2. 焊接温度: +220℃, 10s max
welding temperature:+220℃, 10s max
- 三. 材质:
Material
3-1. 塑胶: PBT(Black) UL94V-0
plastic: PBT(Black) UL94V-0
3-2. 插针: 黄铜
contact pin: Brass/Gold plated

浙江博穆精密电子有限公司				
图号 DOCUMENT NUMBER		'2.54-2x6A-H8.5		
料号 MATERIALS NUMBER				
制图 DRAWER	Yang	Scale 比例	1:1	
审查 EXAMINE	Sun	Unit 单位	MM	
日期 DATE	2026.4.28	第三角投影 THIRD ANGLE PROJECTION		