
Floyd Bell Inc
SOUND SOLUTIONS

Ultra Series
UW-09-515-S(S)D





More Information


UL Recognized

RoHS Rohs Compliant

Specifications

Mounting	Panel Mount
Operating Mode	Ultra Loud Slow Dual Function: Warble/Continuous
Operating Voltage	5-15 Vdc
Operating Frequency	2100±250 Hz Center
Typical Operating Current	35 mA at 5 Vdc 80 mA at 15 Vdc
Typical Sound Pressure	97 ±5 dB(A) at 5 Vdc at 24 inches (61 cm), at 25°C 109 ±5 dB(A) at 15 Vdc at 24 inches (61 cm), at 25°C
Termination	Quick Connect Blades with Screws
Termination Strength	Pull test with a maximum of 22 pounds (10 kg) load
Operating Temperature	-20_C to +65_C
Storage Temperature	-40_C to +85_C
Surge Voltage	20% over maximum rated voltage for less than 5 minutes
Reverse Voltage Protection	To the maximum operating voltage
Construction Materials	Case- Plastic _NORYL_ N-190, Flame Retardant UL 94-VO, Black Internal Circuit- Audio-oscillator and piezoelectric driver Potting- 2 parts epoxy resin or silicone, black Diaphragm- Stainless Steel 304
Gasket	Gasket (sold separately) 0.062" thick, 60 Durometer Neoprene
Construction Materials	ASTM B117 Certified - Withstands exposure to salt spray for 300 hours IP 68 Certified - Withstands water submergence and dust exposure Humidity- 95% relative humidity at +40_C continuously for 100 hours. Vibration- Withstands vibration between 0 and 55 Hz. on all axes.
Life Expectancy	10 years under normal operating conditions.
Warranty	For a period of two years from the date of manufacture under normal operating conditions.
Notes	This product is not intended as a life safety device.
Terms and Conditions of Sale	Link here

Dimensions


REAR
SIDE
RING
FRONT
3 SCREWS
#6-32 x 1/4"
PNH SLOT SS
WARBLE TONE
NEGATIVE
CONSTANT TONE
NEGATIVE
POSITIVE
0.43in
[10.9mm]
0.89in
[22.7mm]
0.46in
[11.7mm]
1.11in
[28.3mm]
1.125-24 UNF THREADS
FOR REFERENCE ONLY
0.31in
[7.9mm]
1.28in
[32.5mm]
ϕ 1.41in
[35.8mm]
FLOYD BELL, INC.
COLUMBUS, OHIO
TOLERANCES ARE: ±0.03in.
[±0.76mm]
PANEL MOUNTING
1.1250in
[28.575mm]
FITS PANELS UP TO
0.25in [6.35mm] THICK
"S" TERMINALS
STAINLESS STEEL SCREWS
6 X 32, 0.25 (6.4) LONG
0.250 (6.4)
0.032 (0.81)
0.312 (7.9)
0.760 (19.3)
6/32 THREAD
0.312 (7.9)