
Pin Spacing: 5.08mm
Orientation: Horizontal Header
Clamp Type: –
Design: Single Mold - Closed End



PHPxx-5.08

ELECTRICAL

	Current	Voltage	Wire Range
cULus E178356	12A	300V	–
IEC	16A	450V	–


INSTALLATION DATA

Screw Size	–	**PCB Hole Size**	1.5mm
Torque	–	**Stripping Lgth.**	–


MATERIAL

Body	Polyamide	**Screw**	–
Flammability Class	UL94V-0	**Terminal**	Tin-Plated Brass
Temperature Limit	105˚C UL 125˚C IEC	**Clamp**	–
Color	Green		

No. Poles	Cat. #	Length (mm)	Std. Pk.
2	PHP02-5.08	12.2	100
3	PHP03-5.08	17.2	100
4	PHP04-5.08	22.3	50
5	PHP05-5.08	27.4	50
6	PHP06-5.08	32.5	50
7	PHP07-5.08	37.6	50
8	PHP08-5.08	42.6	50
9	PHP09-5.08	47.7	50
10	PHP10-5.08	52.8	50
11	PHP11-5.08	57.9	50
12	PHP12-5.08	63.0	50
13	PHP13-5.08	68.0	20
14	PHP14-5.08	73.1	20
15	PHP15-5.08	78.2	20
16	PHP16-5.08	83.3	20
17	PHP17-5.08	88.4	20
18	PHP18-5.08	93.4	20
19	PHP19-5.08	98.5	20
20	PHP20-5.08	103.6	20
21	PHP21-5.08	108.7	20
22	PHP22-5.08	113.8	20
23	PHP23-5.08	118.6	20
24	PHP24-5.08	123.9	20



Pin Spacing: 5.08mm
Orientation: 45° Angle Header
Design: Single Mold - Open End



PIxx-5.08

ELECTRICAL

	Current	Voltage	Wire Range
cULus E178356	12A	300V	–
IEC	16A	450V	–

INSTALLATION DATA

Screw Size	–	**PCB Hole Size**	1.5mm
Torque	–	**Stripping Lgth.**	–

MATERIAL

Body	Polyamide	**Screw**	–
Flammability Class	UL94V-0	**Terminal**	Tin-Plated Brass
Temperature Limit	105˚C UL 125˚C IEC	**Clamp**	–
Color	Green		

No. Poles	Cat. #	Length (mm)	Std. Pk.
2	PI02-5.08	10.2	100
3	PI03-5.08	15.2	100
4	PI04-5.08	20.3	50
5	PI05-5.08	25.4	50
6	PI06-5.08	30.5	50
7	PI07-5.08	35.6	50
8	PI08-5.08	40.6	50
9	PI09-5.08	45.7	50
10	PI10-5.08	50.8	50
11	PI11-5.08	55.9	50
12	PI12-5.08	61.0	50
13	PI13-5.08	66.0	20
14	PI14-5.08	71.1	20
15	PI15-5.08	76.2	20
16	PI16-5.08	81.3	20
17	PI17-5.08	86.4	20
18	PI18-5.08	91.4	20
19	PI19-5.08	96.5	20
20	PI20-5.08	101.6	20
21	PI21-5.08	106.7	20
22	PI22-5.08	111.8	20
23	PI23-5.08	116.8	20
24	PI24-5.08	121.9	20

