



Model Description of Amass Products



AMASS SPECIFICATION

Version No.: V1.2

- Item No.: XT60U-F
- Patent No.: 201530451153.3
- Customer Drawing



■ Material & Parameter

Item No.	XT60U-F	Contact Resistance CR	0.45mΩ
COLOR	2 3	Rated Voltage	DC 500V
Metal Material	Brass Gold Plated	Rated Current RC	30A
Plastic Material	PA	Max Continuous Current MC	60A
FR LEVEL	UL94 V0	Recommend Use Times	1000 TIMES
Recommend USE	BATTERY	Cable SPEC.	12AWG
CERTIFICATION	/	TEMPERATURE	-20℃ to 120℃

★Note: The test data may change during the test, please refer to the latest data.

Changzhou Amass Electronics Co., Ltd.

Add: No.6 Jinyang Oceanic Pearl Road, Wujin District, Changzhou City, Jiangsu Province
(QingYang Road, Lijia Town, Wujin Dis. Changzhou City, Jiangsu Pro.)

Tel: 86 519 86731695

Fax: 86 519 86735861

Zip: 213176

E-mail: hzy@china-amass.com

Web: www.china-amass.com