
MSWSE-005-10S

Silicon PIN Diode Switch Element


Rev. V1

Features

- Small Size (40 x 25 mils)
- Broadband Performance up to 6 GHz
- Supports up to 5 W Power
- Low Insertion Loss: 0.3 dB
- RoHS* Compliant



(0402)
Molded Plastic DFN Package



Description

The MSWSE-005-10S is a PIN diode SPST switch element designed for medium incident power applications up to 5 W CW It has low insertion loss and medium isolation below 6GHz.

Electrical Specifications: T_A = +25°C

Parameter	Test Conditions	Min.	Typ.	Max.	Units
Breakdown Voltage	I_R = 10 µA	200	—	—	V
Forward Voltage	I_F = 50 mA	—	980	1050	mV
Junction Capacitance	V_R = 50 V, 1 MHz	—	0.035	0.05	pF
Total Capacitance	V_R = 50 V, 1 MHz	—	0.08	0.12	pF
Series Resistance	I_F = 30 mA, 500 MHz I_F = 100 mA, 500 MHz	—	2.0 1.4	2.5 1.8	Ω
Lifetime	I_F = 10 mA, I_R = 6 mA , 50%	—	180	300	ns
Insertion Loss	I_F = 50 mA, <2.7 GHz I_F = 50 mA, <6.0 GHz	—	0.25 0.50	0.4 —	dB
Isolation	V_R = 50 V, <2.7 GHz V_R = 50 V, <6.0 GHz	13 —	16 10	—	dB
Input Return Loss	V_R = 50 V, <6.0 GHz	16	20	—	dB

* Restrictions on Hazardous Substances, European Union Directive 2011/65/EU.

MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.
Visit www.macom.com for additional data sheets and product information.

For further information and support please visit:
https://www.macom.com/support


Absolute Maximum Ratings[1,2]

Parameter	Absolute Maximum
Breakdown Voltage	200 V
Forward Current	200 mA
Thermal Resistance	50°CW
Junction Temperature	+175°C
Storage Temperature	-55°C to +150°C
Solder Temperature	+260°C per JEDEC STD-J-20C

1. Exceeding any one or combination of these limits may cause permanent damage to this device.
2. MACOM does not recommend sustained operation near these survivability limits.


Junction Temperature vs. Input Power

1.3 GHz, T_A = 25°C, PCB Mounted on Heat Sink




Typical RF Performance Curves @ +25°C


Insertion Loss




Isolation



Input Return Loss




Series Resistance vs. Current, 500 MHz




MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.
Visit www.macom.com for additional data sheets and product information.

For further information and support please visit:
https://www.macom.com/support

PCB Layout



Outline



Dimensions: inches [mm]
Finish: 300 micro inches matte tin,
annealed 1 hour @ 150°C

MACOM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.
Visit www.macom.com for additional data sheets and product information.

For further information and support please visit:
https://www.macom.com/support

MACOM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with MACOM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.