

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT – By – ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	REVISED PER ECO-12-014453	13SEP12	KH	DR
	F4	REVISED PER ECO-17-008806	16FEB2018	RS	DR





1. STAMP AMP APPROX AS SHOWN
2. TIN PLATE 0.00254 [.000100] MIN THK PER ASTM B-545
3. NICKEL PLATE 0.00762 [.000300] MIN THK PER QQ-N-290
4. COPPER PER ASTM B-152, ANNEALED
5. NOTE DELETED
6. NOTE DELETED

QTY	FINISH	PACKAGING	PART NO
1000	3	LOOSE PIECE	2-31425-3
5000	2	ON TAPE	2-31425-2
1000	2	LOOSE PIECE	31425

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C [338°F]
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	VOLTAGE RATING: N/A
FOR ORDER ENTRY	1-800-526-5142	CIRCULAR MIL AREA: 0.1-0.41mm ²[202-810] STRANDED
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		

1471-9 (1/15)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± 0.127[.005]
4 PLC ± –
ANGLES ± –

MATERIAL COPPER 4

FINISH SEE TABLE

DWN TA BRINKMAN 2-2-93
CHK DA PATTERSON 2-2-93
APVD DA PATTERSON 2-2-93
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT

TE Connectivity Ltd.

NAME TERMINAL, RING TONGUE, BUDGET WIRE SIZE 26-22 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-31425	—

CUSTOMER DRAWING | SCALE 10:1 | SHEET 1 OF 1 | REV F4

31425