






Specifications

A. Material

Plastic cement: PBT, White
Contact: Copper Alloy, T=0.23mm
Shell: SPCC, T=0.30mm

B. Plating

Contact Area: 0.5u" Au over 50u' min. Nickel
Solder Tails: 100u" min. Matte Tinover 50u' min. Nickel
Shell: 60u" min. Nickel

C. Electrical

Current Rating: 1.5A/contact terminal
Voltage Rating: 30V
Power Rating: 45W
Contact Resistance: 40mΩ max initial
50mΩ max after test
Dielectric Withstanding Voltage: 100V AC
Insulation Resistance: 100MΩ min.


D. Mechanical & Environmental

Operating Temperature: -25℃ to +85℃
Insertion force: 35.7 N Max
Withdrawal force: 10.2 N Min
Contact retention: 4.5N Min
Durability: 1500 cycles


Pin Numbe	Signal Name
1	VBUS
2	D-
3	D+
4	GND

Part Number			Product Description			
PUBFA-R15A-001			USB 2.0 Receptacle, Type A, Wire Solder, 4 Pin			
DWG.No.	P-UBF-104		Tolerances Unspecified		Units: Metric(mm)	
Revision	A0		X.X ±0.35	X° ±5°		
Designed	Lee	11/25/20	X.XX ±0.25	X.X° ±2°		
Approved	Allen	11/25/20	X.XXX ±0.15			







① PE bag




② 500pcs/bag, and seal it with a sealing machine.




③ 16 bag/case (8K pcs).




⑥ Paste the product or ROHS label as shown.



⑤ The outer box is sealed with transparent adhesive tape in the shape of "H".



④ 8 bag per box * 2, if the last box is added with filler in the space.

Part Number			Product Description					 Connecting the Future www.szywf.com.cn www.szywf.cn
PUBFA-R15A-001			USB 2.0 Receptacle, Type A, Wire Solder, 4 Pin					
DWG.No.			Tolerances Unspecified			Units: Metric(mm)		
Revision	A0		X.X	±0.35	X°	±5°		
Designed	Lee	11/25/20	X.XX	±0.25	X.X°	±2°		
Approved	Allen	11/25/20	X.XXX	±0.15	