CARMEN-M-C-WHT

~35° wide beam. Assembly with holder C compatible with LEDiL HEKLA. White version.



SPECIFICATION:

Dimensions	Ø 69.5 mm
Height	41.5 mm
Fastening	socket
ROHS compliant	yes


MATERIALS:

Component	Type	Material	Colour	Finish
CARMEN-M	Single lens	PMMA	clear	
CARMEN-HLD-C-WHT	Holder	PC	white	

ORDERING INFORMATION:

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CP16938_CARMEN-M-C-WHT » Box size: 476 x 273 x 292 mm	Single lens	150	150	15	6.1

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.



INDEX	PART NO	MATERIAL	COLOUR
1	CARMEN-LENS	PMMA	Clear
2	HEKLA-Socket	PBT	White
3	CARMEN-HLD-C	PC	Black

Tolerances if not otherwise shown
According to DIN ISO 2768-1
Linear measures:
up to 30mm class M, otherwise class C
According to DIN ISO 2768-2
Form and position: class L

THIRD ANGLE PROJECTION:

This drawing is the property of LEDiL Oy. It may not be reproduced, copied or communicated without a written agreement with LEDiL Oy.

Ledil Oy
Joensuunkatu 13
FIN 24240 SALO
Finland

DRAWING TITLE
CARMEN-C_Datasheet

SIZE A3 | PART NUMBER

SCALE 1:1 | WEIGHT | SHEET 1/1

See also our general installation guide: www.ledil.com/installation_guide

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

bridgelux

LED	Vesta DTW 13mm (21W)
FWHM / FWTM	56.0° / 86.0°
Efficiency	79 %
Peak intensity	0.8 cd/lm
LEDs/each optic	1
Light colour	Tunable White

Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 491 Typ L8






bridgelux

LED	Vesta TW 6mm DP
FWHM / FWTM	37.0° / 66.0°
Efficiency	84 %
Peak intensity	1.7 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 504 Typ L8






bridgelux

LED	Vesta TW 9mm (9W) DP
FWHM / FWTM	44.0° / 73.0°
Efficiency	83 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 489 Typ L8







CITIZEN

LED	CLU700/701/702/703
FWHM / FWTM	37.0° / 68.0°
Efficiency	87 %
Peak intensity	1.7 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
F15255_HEKLA-SOCKET-C





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):


CITIZEN

LED	CLU710/711
FWHM / FWTM	42.0° / 70.0°
Efficiency	85 %
Peak intensity	1.5 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

F15859_HEKLA-SOCKET-I






CITIZEN

LED	CLU7B2
FWHM / FWTM	36.0° / 64.0°
Efficiency	90 %
Peak intensity	2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

F15255_HEKLA-SOCKET-C






CREE LEDs

LED	CXA/B 15xx
FWHM / FWTM	44.0° / 75.0°
Efficiency	86 %
Peak intensity	1.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

F15256_HEKLA-SOCKET-D






LUMILEDS

LED	LUXEON CX Plus CoB L08 (Gen2)
FWHM / FWTM	58.0° / 89.0°
Efficiency	85 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

Bender Wirth: 637a Hekla





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

LUMILEDS

LED	LUXEON CX Plus CoB - HD S01H4
FWHM / FWTM	35.0° / 58.0°
Efficiency	88 %
Peak intensity	2.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
Bender Wirth: 634c Hekla






LUMILEDS

LED	LUXEON CX Plus CoB - HD S02H6
FWHM / FWTM	35.0° / 59.0°
Efficiency	89 %
Peak intensity	2.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
Bender Wirth: 634c Hekla






LUMILEDS

LED	LUXEON CX Plus CoB - HD S04H9
FWHM / FWTM	43.0° / 68.0°
Efficiency	88 %
Peak intensity	1.5 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
Bender Wirth: 634c Hekla






LUMILEDS

LED	LUXEON CX Plus CoB L04 / L05 (Gen2)
FWHM / FWTM	50.0° / 77.0°
Efficiency	86 %
Peak intensity	1.1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
Bender Wirth: 637a Hekla





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (MEASURED):


LUMILEDS

LED	LUXEON CX Plus CoB M02 / M03 (Gen2)
FWHM / FWTM	42.0° / 66.0°
Efficiency	87 %
Peak intensity	1.6 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

Bender Wirth: 641a Hekla






LUMILEDS

LED	LUXEON CX Plus CoB S01 (Gen2)
FWHM / FWTM	35.0° / 58.0°
Efficiency	89 %
Peak intensity	2.2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

Bender Wirth: 634c Hekla







LUMINUS

LED	CxM-11 (19x19)
FWHM / FWTM	51.0° / 81.0°
Efficiency	84 %
Peak intensity	1 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

F15859_HEKLA-SOCKET-I






LUMINUS

LED	CXM-3
FWHM / FWTM	35.0° / 64.0°
Efficiency	91 %
Peak intensity	2 cd/lm
LEDs/each optic	1
Light colour	White

Required components:

F15255_HEKLA-SOCKET-C





LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.


OPTICAL RESULTS (MEASURED):

LUMINUS

LED	CXM-4
FWHM / FWTM	35.0° / 65.0°
Efficiency	88 %
Peak intensity	1.9 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
F15255_HEKLA-SOCKET-C






SAMSUNG

LED	LC010T (Tunable White)
FWHM / FWTM	43.0° / 74.0°
Efficiency	82 %
Peak intensity	1.3 cd/lm
LEDs/each optic	1
Light colour	Tunable White

Required components:
C16142_HEKLA-SOCKET-K
Bender Wirth: 501 Typ L8






XICATO

LED	XOB 6 mm
FWHM / FWTM	39.0° / 69.0°
Efficiency	87 %
Peak intensity	1.7 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
F15255_HEKLA-SOCKET-C






XICATO

LED	XOB 9.8 mm
FWHM / FWTM	43.0° / 74.0°
Efficiency	86 %
Peak intensity	1.4 cd/lm
LEDs/each optic	1
Light colour	White

Required components:
F15255_HEKLA-SOCKET-C






LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

OPTICAL RESULTS (SIMULATED):


CITIZEN

LED	CLL02x/CLU02x (LES10)
FWHM / FWTM	44.0° / 69.0°
Efficiency	88 %
Peak intensity	1.5 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	




CREE LEDs

LED	CMU15xx
FWHM / FWTM	54.0° / 86.0°
Efficiency	71 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	
F17438_HEKLA-G2-I	




NICHIA

LED	COB S-Type (LES 7)
FWHM / FWTM	38.0° / 60.0°
Efficiency	84 %
Peak intensity	1.9 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	
F15848_HEKLA-SOCKET-G	



TRIDONIC

LED	SLE G7 LES09
FWHM / FWTM	41.0° / 66.0°
Efficiency	84 %
Peak intensity	1.6 cd/lm
LEDs/each optic	1
Light colour	White
Required components:	
F15255_HEKLA-SOCKET-C	



LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy
Joensuunkatu 13
FI-24240 SALO
Finland

LEDiL Inc.
228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.
405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support
www.ledil.com/
where_to_buy

Shipping locations
Salo, Finland
Hong Kong, China

Distribution Partners
www.ledil.com/
where_to_buy

LEDiL is a registered trademark of LEDiL Oy in the European Union, USA, and certain other countries.