







Specifications:
规格：
Voltage rating:250V AC/DC
额定电压：250V AC/DC
Current rating:3A AC/DC
额定电流：3A AC/DC
Withstanding voltage:800V AC/minute
耐受电压：800V AC/分钟
Temperature range:-40℃-+105℃
温度范围：-40℃-+105℃
Insulation resistance:1000MΩ min
绝缘电阻：1000MΩ Min
Contact resistance:10mΩ Max
接触电阻：10mΩ Max

X2026 W R - 2x04 S - 9T SN
① ② ③ ④ ⑤ ⑥ ⑦


1.Series No
2.Category:W-Wafer
3.Welding Board Angle:R-Stright 90°
4.Row No.Pin No:2xXX-2x02~2x20P
5.Special No:S-With Positioning baffles on both side
6.Material:9T-PA9T UL94V-0
7.Plating:SN-Tin Plated



Recommended P.C.B Layout
(Top Side)
P.C.B thickness=1.0~1.6mm
(Tolerance=0.05)



2 Pin 视图



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	6.00	2.00	12	26.00	22.00
03	8.00	4.00	13	28.00	24.00
04	10.00	6.00	14	30.00	26.00
05	12.00	8.00	15	32.00	28.00
06	14.00	10.00	16	34.00	30.00
07	16.00	12.00	17	36.00	32.00
08	18.00	14.00	18	38.00	34.00
09	20.00	16.00	19	40.00	36.00
10	22.00	18.00	20	42.00	38.00
11	24.00	20.00	/		

X2026WR-2x04S-9TSN	PA9T	Brass	X2026H
PART N0	Material	Material(Pin)	Suitable XKB Housing

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS

ANGLAR	±5°
L≤ 4	±0.2
4<L≤ 16	±0.3
16<L≤ 63	±0.4
L> 63	±0.5

UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector
DWN		VIEW:	PART NO.: X2026WR-2x04S-9TSN
CHKD		UNIT: mm/in	DWG NO.: X-X2026WR-2x04S-9TSN
APPD		SIZE: A4	

WEIGHT	SHEET	REVISION
	1/1	A0