






PCB LAYOUT TOP VIEW

PIN	$\phi 1.0$	$\phi 1.3$	$\phi 1.65$
APPD		✓	

DC-002HB-01	DC-002HB-1-01

SCHEMATIC



电话：0769-82310511-867
邮箱：hooya89@hooya.hk

SPECIFICATION

1. Rating : DC 12V 1A.
2. Contact resistance: $\leq 50\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC500V).
4. Withstanding voltage: 500VAC .
5. Insertion and extraction force: 5-20N.
6. life test: 10,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
8. Sign "*" is importance dimension.

					TOLERANCE					
					UNLESS SPECIFIED					
6	COVER	PBT	1	BLACK	<1.5: $\pm 0.1\text{mm}$	ANGULAR				
5	HOUSING	PBT	1	BLACK	>1.5~5.0: $\pm 0.25\text{mm}$	$\pm 3^{\circ}$				
4	PIN	BRASS	1	CuSn-PLATED	>5.0: $\pm 0.3\text{mm}$		NO	DATE	REVISIONS	BY APPD
3	CURVE PIECE	BRASS	1	Ag-PLATED	TITLE: DC JACK		UNIT : MM		ROHS	DWN
2	SPRING	Mn STEEL	1	CuSn-PLATED	MODEL: DC-002HB-1.3-01		SCALE: 1:1		COMPLIANT	CHK'D
1	FLAT PIECE	BRASS	1	Ag-PLATED	DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 东莞市弘皓电子有限公司				APPD	
NO.	PART NAME	MATERIAL	QTY	FINISHING			PRO.AGL:		REV :A0	