


Mechanical Data


- Case: Molded plastic
- Epoxy: UL 94V-0 rate flame retardant
- Lead: Solderable per MIL-STD-750, method 2026
- Polarity: Color band denotes cathode end except Bipolar
- Mounting position: Any




Features

- Glass passivated chip
- 600 W peak pulse power capability with a 10/1000 μ s waveform, repetitive rate (duty cycle):0.01 %
- High reliability application and automotive grade
- Meet MSL level1, per J-STD-020
- AEC Q101 qualified
- Low leakage
- Uni and Bidirectional unit
- Excellent clamping capability
- Very fast response time
- RoHS compliant

Electrical symbol



Part Number Code



Mechanical Characteristics

Rating	Symbol	Value	Units
Peak power dissipation with a 10/1000 μ s waveform (Fig.4)(Note 1)	P_{PP}	600	W
Power Dissipation on Infinite Heat Sink at $T_L=75^\circ\text{C}$ (Fig.3)	P_D	5.0	W
Peak Forward Surge Current, 8.3ms Single Half Sine Wave (Note 2)	I_{FSM}	100	A
Maximum instantaneous forward voltage at 50 A for unidirectional only ⁽²⁾	V_F	3.5/5.0	V
Operating Temperature Range Storage Temperature Range	T_J , T_{STG}	-55 to 150	$^\circ\text{C}$

Notes:

1. Non-repetitive current pulse, per Fig.2 and derated above $T_A=25^\circ\text{C}$ per Fig. 1.
2. Measured on 8.3ms single half sine wave or equivalent square wave for unidirectional device only, duty cycle=4 per minute maximum.

Electrical Characteristics (T_A=25°C unless otherwise noted)

Type Number		Marking		Reverse Stand-Off Voltage	Breakdown Voltage		Test Current	Max. Clamping Voltage 10/1000µs	Max. Peak Pulse Current 10/1000µs	Reverse Leakage
					V _{RWM}	Min	Max	I _r	V _{C@I_{PP}}	I _{PP}
UNI	BI	UNI	BI	V	V	V	mA	V	A	µA
SMBJ5.0A-AT	SMBJ5.0CA-AT	AEA	KEA	5.0	6.4	7.0	10	9.2	65.3	800
SMBJ6.0A-AT	SMBJ6.0CA-AT	AGA	KGA	6.0	6.67	7.37	10	10.3	58.3	800
SMBJ6.5A-AT	SMBJ6.5CA-AT	AKA	KKA	6.5	7.22	7.98	10	11.2	53.6	500
SMBJ7.0A-AT	SMBJ7.0CA-AT	AMA	KMA	7.0	7.78	8.6	10	12.0	50.0	200
SMBJ7.5A-AT	SMBJ7.5CA-AT	APA	KPA	7.5	8.33	9.21	1	12.9	46.6	100
SMBJ8.0A-AT	SMBJ8.0CA-AT	ARA	KRA	8.0	8.89	9.83	1	13.6	44.2	50
SMBJ8.5A-AT	SMBJ8.5CA-AT	ATA	KTA	8.5	9.44	10.4	1	14.4	41.7	20
SMBJ9.0A-AT	SMBJ9.0CA-AT	AVA	KVA	9.0	10	11.1	1	15.4	39.0	10
SMBJ10A-AT	SMBJ10CA-AT	AXA	KXA	10	11.1	12.3	1	17	35.3	5
SMBJ11A-AT	SMBJ11CA-AT	KZA	AZA	11.0	12.2	13.5	1	18.2	32.97	1
SMBJ12A-AT	SMBJ12CA-AT	LEA	BEA	12.0	13.3	14.7	1	19.9	30.15	1
SMBJ13A-AT	SMBJ13CA-AT	LGA	BGA	13.0	14.4	15.9	1	21.5	27.91	1
SMBJ14A-AT	SMBJ14CA-AT	LKA	BKA	14.0	15.6	17.2	1	23.2	25.86	1
SMBJ15A-AT	SMBJ15CA-AT	LMA	BMA	15.0	16.7	18.5	1	24.4	24.59	1
SMBJ16A-AT	SMBJ16CA-AT	LPA	BPA	16.0	17.8	19.7	1	26.0	23.08	1
SMBJ17A-AT	SMBJ17CA-AT	LRA	BRA	17.0	18.9	20.9	1	27.6	21.74	1
SMBJ18A-AT	SMBJ18CA-AT	LTA	BTA	18.0	20.0	22.1	1	29.2	20.55	1
SMBJ19A-AT	SMBJ19CA-AT	LBA	BBA	19.0	21.1	23.3	1	30.8	19.49	1
SMBJ20A-AT	SMBJ20CA-AT	LVA	BVA	20.0	22.2	24.5	1	32.4	18.52	1
SMBJ22A-AT	SMBJ22CA-AT	LXA	BXA	22.0	24.4	26.9	1	35.5	16.90	1
SMBJ24A-AT	SMBJ24CA-AT	LZA	BZA	24.0	26.7	29.5	1	38.9	15.42	1
SMBJ26A-AT	SMBJ26CA-AT	MEA	CEA	26.0	28.9	31.9	1	42.1	14.25	1
SMBJ28A-AT	SMBJ28CA-AT	MGA	CGA	28.0	31.1	34.4	1	45.4	13.22	1
SMBJ30A-AT	SMBJ30CA-AT	MKA	CKA	30.0	33.3	36.8	1	48.4	12.40	1
SMBJ33A-AT	SMBJ33CA-AT	MMA	CMA	33.0	36.7	40.6	1	53.3	11.26	1
SMBJ36A-AT	SMBJ36CA-AT	MPA	CPA	36.0	40.0	44.2	1	58.1	10.33	1
SMBJ40A-AT	SMBJ40CA-AT	MRA	CRA	40.0	44.4	49.1	1	64.5	9.30	1
SMBJ43A-AT	SMBJ43CA-AT	MTA	CTA	43.0	47.8	52.8	1	69.4	8.65	1
SMBJ45A-AT	SMBJ45CA-AT	MVA	CVA	45.0	50.0	55.3	1	72.7	8.25	1
SMBJ48A-AT	SMBJ48CA-AT	MXA	CXA	48.0	53.3	58.9	1	77.4	7.75	1
SMBJ51A-AT	SMBJ51CA-AT	MZA	CZA	51.0	56.7	62.7	1	82.4	7.28	1


Electrical Characteristics

Type Number		Marking		Reverse Stand-Off Voltage	Breakdown Voltage		Test Current	Max. Clamping Voltage 10/1000µs	Max. Peak Pulse Current 10/1000µs	Reverse Leakage	
					V _{RWM}	V _{BR} @I _T					
				UNI		BI	UNI	BI	V	Min	Max
				V	V	V	mA	V	A	µA	
SMBJ54A-AT	SMBJ54CA-AT	NEA	DEA	54.0	60.0	66.3	1	87.1	6.89	1	
SMBJ58A-AT	SMBJ58CA-AT	NGA	DGA	58.0	64.4	71.2	1	93.6	6.41	1	
SMBJ60A-AT	SMBJ60CA-AT	NKA	DKA	60.0	66.7	73.7	1	96.8	6.20	1	
SMBJ64A-AT	SMBJ64CA-AT	NMA	DMA	64.0	71.1	78.6	1	103.0	5.83	1	
SMBJ70A-AT	SMBJ70CA-AT	NPA	DPA	70.0	77.8	86.0	1	113.0	5.31	1	
SMBJ75A-AT	SMBJ75CA-AT	NRA	DRA	75.0	83.3	92.1	1	121.0	4.96	1	
SMBJ78A-AT	SMBJ78CA-AT	NTA	DTA	78.0	86.7	95.8	1	126.0	4.76	1	
SMBJ85A-AT	SMBJ85CA-AT	NVA	DVA	85.0	94.4	104.0	1	137.0	4.38	1	
SMBJ90A-AT	SMBJ90CA-AT	NXA	DXA	90.0	100.0	111.0	1	146.0	4.11	1	
SMBJ100A-AT	SMBJ100CA-AT	NZA	DZA	100.0	111.0	123.0	1	162.0	3.70	1	
SMBJ110A-AT	SMBJ110CA-AT	PEA	EEA	110.0	122.0	135.0	1	177.0	3.39	1	
SMBJ120A-AT	SMBJ120CA-AT	PGA	EGA	120.0	133.0	147.0	1	193.0	3.11	1	
SMBJ130A-AT	SMBJ130CA-AT	PKA	EKA	130.0	144.0	159.0	1	209.0	2.87	1	
SMBJ140A-AT	SMBJ140CA-AT	PBA	EBA	140.0	155.0	171.0	1	226.8	2.65	1	
SMBJ150A-AT	SMBJ150CA-AT	PMA	EMA	150.0	167.0	185.0	1	243.0	2.47	1	
SMBJ160A-AT	SMBJ160CA-AT	PPA	EPA	160.0	178.0	197.0	1	259.0	2.32	1	
SMBJ170A-AT	SMBJ170CA-AT	PRA	ERA	170.0	189.0	209.0	1	275.0	2.18	1	


Notes: For bidirectional type having V_R of 10V and less, the I_R limit is double.

I-V Curve Characteristics

Uni-directional



Bi-directional



P_{PPM} Peak Pulse Power Dissipation -- Max power dissipation

V_R Stand-off Voltage -- Maximum voltage that can be applied to the TVS without operation

V_{BR} Breakdown Voltage -- Maximum voltage that flows through the TVS at a specified test current (I_T)

V_C Clamping Voltage -- Peak voltage measured across the TVS at a specified I_{ppm} (peak impulse current)

I_R Reverse Leakage Current -- Current measured at V_R

V_F Forward Voltage Drop for Uni-directional

Ratings and Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

Figure 1 - Pulse Derating Curve




Figure 2 - Pulse Waveform




Figure 3 - Steady State Power Derating Curve




Figure 4 - Peak Pulse Power Rating Curve




Figure 5 - Maximum Non-Repetitive Surge Current






Figure 6 - Typical Junction Capacitance




Soldering Parameters - Reflow Soldering (Surface Mount Devices)




Reflow Condition		Pb - Free assembly
Pre Heat	-Temperature Min ($T_{s(min)}$)	150°C
	-Temperature Max ($T_{s(max)}$)	200°C
	- Time (min to max) (t_s)	60 -180 Seconds
Average ramp up rate (Liquids Temp T_L to peak)		3°C/second max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/second max
Reflow	- Temperature (T_L) (Liquids)	217°C
	- Time (min to max) (t_s)	60 -150 Seconds
Peak Temperature (T_P)		260 +0/-5°C
Time within 5°C of actual peak Temperature (t_p)		20 - 40 Seconds
Ramp-down Rate		6°C/second max
Time 25°C to peak Temperature (T_P)		8 minutes Max
Do not exceed		260°C

Part Marking System





DO-214AA (SMB) Dimensions



DIM	Millimeters		Inches	
	Min	Max	Min	Max
A	1.96	2.20	0.078	0.086
B	4.35	4.85	0.171	0.191
C	3.30	3.75	0.130	0.148
D	2.13	2.44	0.084	0.096
E	0.75	1.51	0.030	0.059
G	5.10	5.50	0.201	0.217
I	2.26	-	0.089	-
J	2.16	-	0.085	-
K	-	2.74	-	0.107
L	2.16	-	0.085	-

Taping and Reel Specifications



Symbol	Millimeters	Inches
W	12±0.3	0.472±0.012
P	8±0.1	0.315±0.004
F	5.5±0.1	0.217±0.004
E	1.75±0.1	0.069±0.004
D	1.5+0.1/-0.0	0.059+0.004/-0.0
P0	4±0.1	0.157±0.004
P2	2±0.1	0.079±0.004
D0	16.7±0.15	0.657±0.006
D1	Φ330±2.0	12.99±0.079
W1	16.0±1.0	0.63±0.039

Part Number	Component package	Quantity	Packaging option	Packaging specification
SMBJXXXA/CA-AT	DO-214AA(SMB)	3000	Tape&Reel-12mm/13"tape	EIA STD RS-481