



SIGN	DATE	DESCRIPTION	APPROVER
1	01/10'09	The design is changed	Jacke
2	04.20'09	The operating temperature is changed	Jacke
3	2010.01.12	Add cULus standard	Jacke
4	2010.03.31	Add the 2p mark	Jacke
5	2010.04.26	The current rating is changed from 10A to 20A	Jacke
6	2014.09.27	The current rating is changed from 20A to 10A	Evan
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			










SECTION P-P



PCB LAYOUT

DIM		TOL			
		2P-6P	7P-12P	13P-18P	19P-24P
Dim L	(N-1)×5.08+7.08	±0.15	±0.25	±0.30	±0.40
Dim B	(N-1)×5.08	±0.15	±0.25	±0.30	±0.40
Dim C	N×5.08	+0.0 -0.20		+0.0 -0.40	
Dim D	(N-1)×5.08	±0.15	±0.25	±0.30	±0.40

Materials

Item ⓐ Terminal body:Thermoplastic (UL94V-0)

Item ⓑ Female contact:PhBz(CuSn), Tin plated

Item ⓒ Terminal cover:Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 300VAC
- 6 5 Current rating: 10A
- Withstanding Voltage: 1.6kv
- 2 Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus
- Critical dimension: C

V7 xx 5 1 x 1 xxxx G

No. OF POLES
02 2 ploes
03 3 ploes
... ...
24 24 ploes

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer requst. please contact sales department.

G RoHS compliant (lead<4%) In copper Alloy

Amphenol ANYTEK

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

INSPECTION COPY

TITLE	V7 5.08 Series Right-angle				
PART NO.	V7xx51x1xxxxG			DWG NO.	8V70302
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Evan 2014.09.27	Evan 2014.09.27	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: G	

Tolerance	
X.	±0.5
X.X	±0.3
X.XX	±0.1
X°	±1°