

## 1. General Description

---

The 74LVC1G57 is a configurable multiple function gate with Schmitt-trigger inputs. The device can be configured as any of the following logic functions AND, OR, NAND, NOR, XNOR, inverter and buffer; using the 3-bit input. All inputs can be connected directly to  $V_{CC}$  or GND. Inputs can be driven from either 3.3 V or 5 V devices. This feature allows the use of these devices as translators in mixed 3.3 V and 5 V environments.

This device is fully specified for partial power down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing the potentially damaging backflow current through the device when it is powered down.

## 2. Features and Benefits

---

- Wide supply voltage range from 1.65 V to 5.5 V
- Overvoltage tolerant inputs to 5.5 V
- High noise immunity
- $\pm 24$  mA output drive ( $V_{CC} = 3.0$  V)
- CMOS low power dissipation
- Latch-up performance exceeds 200 mA
- Direct interface with TTL levels
- $I_{OFF}$  circuitry provides partial Power-down mode operation
- Complies with JEDEC standard:
  - JESD8-7 (1.65 V to 1.95 V)
  - JESD8-5 (2.3 V to 2.7 V)
  - JESD8B/JESD36 (2.7 V to 3.6 V)
- ESD protection:
  - HBM ANSI/ESDA/JEDEC JS-001 Class 3B exceeds 8000 V
  - CDM ANSI/ESDA/JEDEC JS-002 Class C3 exceeds 2000 V
- Multiple package options


### 3. Ordering Information

Table 1. Ordering information


Type number	Topside marking	Package		
		Name	Description	Quantity
74LVC1G57GV	VHYW	SOT23-6L	SOT23 package, 6 pins 2.92 mm × 1.6 mm; 1.25 mm (Max) height	3000
74LVC1G57GW	VHYW	SOT363	SOT363 package, 6 pins 2.1 mm × 1.25 mm; 1.1 mm (Max) height	3000

**MARKING INFORMATION**

NOTE: YW = Data Code.



### 4. Function Diagram



## 5. Pinning Information

### 5.1. Pinning




Fig. 2. Top view pin configuration SOT23-6 and SOT363

### 5.2. Pin description

Table 2. Pin description

Symbol	Pin	Description
B	1	Data input
GND	2	Ground (0V)
A	3	Data input
Y	4	Data output
V <sub>CC</sub>	5	Supply voltage
C	6	Data input

## 6. Functional Description

**Table 3. Function table**


H = HIGH voltage level; L = LOW voltage level.

Input			Output
C	B	A	Y
L	L	L	H
L	L	H	L
L	H	L	H
L	H	H	L
H	L	L	L
H	L	H	L
H	H	L	H
H	H	H	H

### 6.1. Logic configurations

**Table 4. Function selection table**

Logic function	Figure
2-input AND	see Fig. 3
2-input AND with both inputs inverted	see Fig. 6
2-input NAND with inverted input	see Fig. 4 and Fig. 5
2-input OR with inverted input	see Fig. 4 and Fig. 5
2-input NOR	see Fig. 6
2-input NOR with both inputs inverted	see Fig. 3
2-input XNOR	see Fig. 7
Inverter	see Fig. 8
Buffer	see Fig. 9



## 7. Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

**Table 5. Absolute Maximum Ratings**

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND.

Symbol	Parameter	Conditions	Min	Max	Unit
$V_{CC}$	supply voltage		-0.5	6.5	V
$I_{IK}$	input clamping current	$V_I < 0\text{ V}$	-50		mA
$V_I$	input voltage	[1]	-0.5	6.5	V
$I_{OK}$	output clamping current	$V_O > V_{CC}$ or $V_O < 0\text{ V}$		$\pm 50$	mA
$V_O$	output voltage	Active mode [1]	-0.5	6.5	V
		Power-down mode; $V_{CC} = 0\text{ V}$ [1]	-0.5	6.5	V
$I_O$	output current	$V_O = 0\text{ V}$ to $V_{CC}$		$\pm 50$	mA
$I_{CC}$	supply current			100	mA
$I_{GND}$	ground current		-100		mA
$P_{tot}$	total power dissipation	$T_{amb} = -40\text{ °C}$ to $+125\text{ °C}$		250	mW
$T_{stg}$	storage temperature		-65	150	°C

[1] The input and output voltage ratings may be exceeded if the input and output current ratings are observed.

## 8. Recommended Operating Conditions

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. EnergyMath does not recommend exceeding them or designing to Absolute Maximum Ratings.

**Table 6. Recommended Operating Conditions**

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$V_{CC}$	supply voltage		1.65		5.5	V
$V_I$	input voltage		0		5.5	V
$V_O$	output voltage	Active mode	0		$V_{CC}$	V
		Power-down mode; $V_{CC} = 0\text{ V}$	0		5.5	V
$T_{amb}$	ambient temperature		-40		125	°C

## 9. Static Characteristics

**Table 7. Static characteristics**

At recommended operating conditions. Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
V <sub>OH</sub>	HIGH-level output voltage	V <sub>I</sub> = V <sub>T+</sub> or V <sub>T-</sub>						
		I <sub>O</sub> = -100µA; V <sub>CC</sub> = 1.65 V to 5.5 V	V <sub>CC</sub> - 0.1			V <sub>CC</sub> - 0.1		V
		I <sub>O</sub> = -4 mA; V <sub>CC</sub> = 1.65 V	1.2	1.6		0.95		V
		I <sub>O</sub> = -8 mA; V <sub>CC</sub> = 2.3 V	1.9	2.2		1.7		V
		I <sub>O</sub> = -12 mA; V <sub>CC</sub> = 2.7 V	2.2	2.5		1.9		V
		I <sub>O</sub> = -24 mA; V <sub>CC</sub> = 3.0 V	2.3	2.7		2.0		V
		I <sub>O</sub> = -32 mA; V <sub>CC</sub> = 4.5 V	3.8	4.2		3.4		V
V <sub>OL</sub>	LOW-level output voltage	V <sub>I</sub> = V <sub>T+</sub> or V <sub>T-</sub>						
		I <sub>O</sub> = 100µA; V <sub>CC</sub> = 1.65 V to 5.5 V			0.10		0.10	V
		I <sub>O</sub> = 4 mA; V <sub>CC</sub> = 1.65 V		0.02	0.45		0.70	V
		I <sub>O</sub> = 8 mA; V <sub>CC</sub> = 2.3 V		0.06	0.30		0.45	V
		I <sub>O</sub> = 12 mA; V <sub>CC</sub> = 2.7 V		0.12	0.40		0.60	V
		I <sub>O</sub> = 24 mA; V <sub>CC</sub> = 3.0 V		0.28	0.55		0.80	V
		I <sub>O</sub> = 32 mA; V <sub>CC</sub> = 4.5 V		0.34	0.55		0.80	V
I <sub>I</sub>	input leakage current	V <sub>I</sub> = 5.5 V or GND ; V <sub>CC</sub> = 0 V to 5.5 V		±0.1	±1		±1	µA
I <sub>OFF</sub>	power-off leakage current	V <sub>CC</sub> = 0V ; V <sub>I</sub> or V <sub>O</sub> = 5.5 V		±0.1	±2		±2	µA
I <sub>CC</sub>	supply current	V <sub>I</sub> = 5.5V or GND ; I <sub>O</sub> = 0A ; V <sub>CC</sub> = 5.5V		0.1	4		4	µA
ΔI <sub>CC</sub>	additional supply current	per pin ; V <sub>CC</sub> = 2.3V to 5.5V ; V <sub>I</sub> = V <sub>CC</sub> - 0.6V ; I <sub>O</sub> = 0A		5	500		500	µA
C <sub>I</sub>	input capacitance	V <sub>CC</sub> = 3.3V ; V <sub>I</sub> = GND to V <sub>CC</sub>		5				pF

 [1]All typical values are measured at T<sub>amb</sub> = 25°C.

## 10. Dynamic Characteristics

**Table 8. Dynamic characteristics**

Voltages are referenced to GND (ground = 0 V); for test circuit see Fig. 11.

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
$t_{pd}$	propagation delay	A, B, C to Y; see Fig. 10 [2]						
		$V_{CC} = 1.65 \text{ V to } 1.95 \text{ V}$	4.0	15.7	26	4.0	26.5	ns
		$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$	2.5	9.5	14	2.5	14.5	ns
		$V_{CC} = 3.0 \text{ V to } 3.6 \text{ V}$	2.0	7.1	9	2.0	9.5	ns
		$V_{CC} = 4.5 \text{ V to } 5.5 \text{ V}$	1.5	2.9	5	1.5	5.5	ns
$C_{PD}$	power dissipation capacitance	$V_{CC} = 3.3 \text{ V}$ $V_I = \text{GND to } V_{CC}$ [3]		25				pF

[1] Typical values are measured at nominal at  $T_{amb} = 25 \text{ °C}$  and  $V_{CC} = 1.8 \text{ V}, 2.5 \text{ V}, 3.3 \text{ V}$  and  $5.0 \text{ V}$  respectively.

[2]  $t_{pd}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ .

[3]  $C_{PD}$  is used to determine the dynamic power dissipation ( $P_D$  in  $\mu\text{W}$ ).

$P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma(C_L \times V_{CC}^2 \times f_o)$  where:

$f_i$  = input frequency in MHz;

$f_o$  = output frequency in MHz;


$C_L$  = output load capacitance in pF;

$V_{CC}$  = supply voltage in V;

$N$  = number of inputs switching;


$\Sigma(C_L \times V_{CC}^2 \times f_o)$  = sum of outputs.

### 10.1. Waveforms and test circuit



**Table 9. Measurement points**

Supply Voltage	Input	Output
$V_{CC}$	$V_M$	$V_M$
1.65 V to 1.95 V	$0.5V_{CC}$	$0.5V_{CC}$
2.3 V to 2.7 V	$0.5V_{CC}$	$0.5V_{CC}$
3.0 V to 3.6 V	1.5 V	1.5 V
4.5 V to 5.5 V	$0.5V_{CC}$	$0.5V_{CC}$


**Table 10. Test data**

Supply voltage	Input		Load		$V_{EXT}$
$V_{CC}$	$V_I$	$t_r = t_f$	$C_L$	$R_L$	$t_{PLH}, t_{PHL}$
1.65 V to 1.95 V	$V_{CC}$	$\leq 2.0$ ns	15 pF	500 $\Omega$	open
2.3 V to 2.7 V	$V_{CC}$	$\leq 2.0$ ns	15 pF	500 $\Omega$	open
3.0 V to 3.6 V	3 V	$\leq 2.5$ ns	15 pF	500 $\Omega$	open
4.5 V to 5.5 V	$V_{CC}$	$\leq 2.5$ ns	15 pF	500 $\Omega$	open

## 11. Transfer Characteristics


**Table 11. Transfer characteristics**

At recommended operating conditions. Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	-40 °C to +85 °C			-40 °C to +125 °C		Unit
			Min	Typ[1]	Max	Min	Max	
V <sub>T+</sub>	positive-going threshold voltage	see Fig. 12, Fig. 13, Fig. 14 and Fig. 15						
		V <sub>CC</sub> = 1.8 V	0.70	1.09	1.20	0.67	1.20	V
		V <sub>CC</sub> = 2.3 V	1.11	1.36	1.60	1.08	1.60	V
		V <sub>CC</sub> = 3.0 V	1.50	1.69	2.00	1.47	2.00	V
		V <sub>CC</sub> = 4.5 V	2.16	2.39	2.74	2.13	2.74	V
		V <sub>CC</sub> = 5.5 V	2.61	2.86	3.33	2.58	3.33	V
V <sub>T-</sub>	negative-going threshold voltage	see Fig. 12, Fig. 13, Fig. 14 and Fig. 15						
		V <sub>CC</sub> = 1.8 V	0.30	0.6	0.72	0.30	0.75	V
		V <sub>CC</sub> = 2.3 V	0.58	0.77	1.00	0.58	1.03	V
		V <sub>CC</sub> = 3.0 V	0.80	1.09	1.30	0.80	1.33	V
		V <sub>CC</sub> = 4.5 V	1.21	1.62	1.90	1.21	1.93	V
		V <sub>CC</sub> = 5.5 V	1.45	1.99	2.29	1.45	2.32	V
V <sub>H</sub>	hysteresis voltage	see Fig. 12, Fig. 13, Fig. 14 and Fig. 15						
		V <sub>CC</sub> = 1.8 V	0.30	0.49	0.62	0.23	0.62	V
		V <sub>CC</sub> = 2.3 V	0.40	0.58	0.80	0.34	0.80	V
		V <sub>CC</sub> = 3.0 V	0.50	0.6	1.00	0.44	1.00	V
		V <sub>CC</sub> = 4.5 V	0.71	0.76	1.20	0.65	1.20	V
		V <sub>CC</sub> = 5.5 V	0.71	0.86	1.40	0.65	1.40	V


 [1] All typical values are measured at T<sub>amb</sub> = 25°C.

### 11.1. Waveforms transfer characteristics




## 12. Package Outline

SOT23-6L



SOT363



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.150	0.350	0.006	0.014
c	0.110	0.175	0.004	0.007
D	2.000	2.200	0.079	0.087
E	1.150	1.350	0.045	0.053
E1	2.150	2.450	0.085	0.096
e	0.650 TYP.		0.026 TYP.	
e1	1.200	1.400	0.047	0.055
L	0.525 REF.		0.021 REF.	
L1	0.260	0.460	0.010	0.018
θ	0°	8°	0°	8°

## 13. Abbreviations

Table 12. Abbreviations

Acronym	Description
CMOS	Complementary Metal-Oxide Semiconductor
DUT	Device Under Test
ESD	ElectroStatic Discharge
HBM	Human Body Model
CDM	Charged Device Model
TTL	Transistor-Transistor Logic

## 14. Revision History

Table 13. Revision history

Document ID	Release Date	Data sheet status	Change notice	Supersedes
74LVC1G57Rev. 1.0	Aug 08, 2024	Product datasheet		