



- SPECIFICATION:**
1. RATING: DC 30V 15A
 2. CONTACT RESISTANCE: 30mΩ MAX(INITIAL), 50mΩ MAX(FINAL).
 3. INSULATION RESISTANCE: 100 MΩ MIN.
 4. WITHSTAND VOLTAGE: 500 VAC
 5. INSERTION FORCE: 30N MAX.
 6. EXTRACTION FORCE: 3N MIN.
 7. DURABILITY: 5,000 CYCLES

no.	DESCRIPTION	MATERIAL	REMARKS	QTY
C	SHELL	C5210	Ni 40u" MIN.	1
B	CENTER PIN	BRASS	GOLD FLASH /Ni 40u" MIN.	1
A	HOUSING	PA10T	BLACK	1

ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	UNSPECIFIED TOLERANCE
	A/0		NEW				

Designed: _____ Checked: _____ Approved: _____ Date: 2021/06/28

MODEL TYPE: DC-331-250 DC JACK

浙江创都电子科技有限公司

PART NO. CAX-DC-1152-200H-XL-331-2.5AU
 UNIT: mm SCALE: 1:1 VIEW: Edition: A/0