



NOTES:  
 MATERIAL:  
 1. HOUSING MATERIAL:GLASS FILLED POLYESTER UL94V-0.  
 2. CONTACT MATERIAL:PHOSPHOR BRONZE  $\phi=0.46\text{mm}$ .  
 3. PLATING :SELECTING GOLD PLATING  $3\mu\sim 50\mu$ OVER NICKEL  
 ELECTRICAL:  
 1. VOLTAGE RATING:125 VAC RMS.  
 2. CURRENT RATING:1.5 AMP.  
 3. CONTACT RESISTANCE:30 MILLIOHMS MAX.  
 4. INSULATION RESISTANCE:500 MEGOHMS MIN @500V DC.  
 5. DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 50Hz. 1MIN.  
 MECHANICAL:  
 1. DURRABILITY: :750 CYCLES MIN.  
 2. PCB RETENTION PRE-SOLDER:1 LB MIN.  
 ENVIRONMENTAL:  
 1. STORAGE:-40°C TO 85°C.  
 2. OPERATION:0°C TO 70°C.

			GENERAL TOLERANCE	制图 DRAWING	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	网络插座 (无灯全塑)	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	HC-RJ45-5224-1-6	单位 UNITS	mm
1	初版发行		X.XXX ±0.10	投影 Projection		材料 MATERIAL	页次 SHEET	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					