


SIGN	DATE	DESCRIPTION	APPROVER
1	10/27'12	Change the dimensional tolerance	Jacky
2	10/27'12	Change the screw plating specification	Jacky
3	10/27'12	Change the eletrical specification	Jacky
4	06/05'14	change the structure	Guoxue
5	06/05'14	Change the dimensional tolerance	Guoxue
6	08/26'14	The dimensional tolerance is changde from17.4±0.30 to17.4$^{+0.60}_{-0.30}$	Airy min
		THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!	








MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:	300 V, 20 A
WITHSTAND VOLTAGE:	AC 2000 V/Min
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V
3 OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C
SCREW TORQUE VALUE:	12 Lb-In.
WIRE RANGE:	22 - 12AWG
1) MOLDED PARTS:	THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t
2 3) TERMINAL SCREWS:	STEEL, M3.5
4) COVER MATERIAL:	PC
APPROVAL:	c UL us
Critical dimension:	▽

PART No.:

YK501 xx 2 x x 00G

- xx — NO. OF POLES
  - 04: 4 POLES
  - 05: 5 POLES
  - 06: 6 POLES
  - :
  - 30: 30 POLES
- 2 — TERMINAL & SCREW PLATED
  - 0: TERMINAL & SCREW: G/F
  - 2 1: TERMINAL: G/F, SCREW: Zinc
  - 2: TERMINAL: Sn, SCREW: G/F
  - 2 3: TERMINAL: Sn, SCREW: Zinc
- x — MARK
  - 0: "@" MARK
  - 1: "ANY" MARK
- 00G — G:RoHS compliant(lead<4%) in copper alloy



PCB Layout(TOP VIEW)

N=Number of contacts

Dimension A&B

DIM A	N×9.5+3.0
DIM B	(N-1)×9.5

5 1

Poles	Tolerance
4P	±0.20
5P-10P	±0.30
11P-24P	±0.40
25P-30P	±0.60

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-501 W/O Flange&With Cover Series (4P-30P)				
PART NO.	YK501xx2xx00G			DWG NO.	8YK0002-501
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Airy min 2014.08.26	Airy min 2014.08.26	UNIT: mm / SCALE: NONE / SHEET: 01/01 / REV.: E	

Tolerance	
X.	±0.50
X.X	±0.30
X.XX	±0.10
X°	±1°