



-20V/80mΩ@-4.5V P-Channel MOSFET

Features

- $V_{DS(max)} = -20V$
- $I_{D(max)} = -2.5A$
- $R_{DS(ON)} = 80m\Omega(Typ.)@V_{GS} = -4.5V$
- $R_{DS(ON)} = 110m\Omega(Typ.)@V_{GS} = -2.5V$
- Advanced Trench Technology
- Excellent $R_{DS(ON)}$ and Low Gate Charge
- Lead free product is acquired

Maximum Ratings ($T_c = 25^\circ C$, Unless Otherwise Noted)

Parameters	Symbol	Limits	Unit
Drain-Source Voltage	V_{DS}	-20	V
Gate-Source Voltage	V_{GS}	± 12	V
Drain Current - Continuous($T_c = 25^\circ C$)	I_D	-2.5	A
Drain Current - Continuous($T_c = 100^\circ C$)		-1.6	A
Drain Current - Pulsed	I_{DM}^1	-10	A
Power Dissipation($T_c = 25^\circ C$)	P_D	1	W
Power Dissipation - Derate above $25^\circ C$		0.008	W/ $^\circ C$
Storage Temperature Range	T_{STG}	-55~150	$^\circ C$
Operating Junction Temperature Range	T_j	-55~150	$^\circ C$



Thermal Characteristics

Parameter	Symbol	Max.	Typ.	Unit
Thermal Resistance Junction to ambient	$R_{\theta JA}$	---	125	$^\circ C/W$

Applications

- PWM Applications
- Power Management
- Load Switch

SOT23 Pin Configuration



Note:

1. Repetitive Rating: Pulsed width limited by maximum junction temperature.
2. The data tested by pulsed, pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.
3. Essentially independent of operating temperature.



Electrical Characteristics(T_j = 25°C, Unless Otherwise Noted)

Off Characteristics						
Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Drain to Source Breakdown Volage	BV _{DSS}	V _{GS} =0V, I _D =-250μA	-20	---	---	V
Drain-Source Leakage Current	I _{DSS}	V _{DS} =-20V, V _{GS} =0V, T _J =25℃	---	---	-1	μA
Gate-Source Leakage Current	I _{GSS}	V _{DS} =0V, V _{GS} =±12V	---	---	±100	nA
On Characteristics						
Static Drain-Source On-Resistance	R _{DS(ON)}	V _{GS} =-4.5V, I _D =-2.5A	---	80	104	mΩ
		V _{GS} =-2.5V, I _D =-1.5A	---	110	154	
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =-250μA	-0.3	-0.7	-1.5	V
Dynamic And Switching Characteristics						
Total Gate Charge ^{2,3}	Q _g	V _{DS} =-10V, V _{GS} = -4.5V, I _D =-2.5A	---	2.9	---	nC
Gate-Source Charge ^{2,3}	Q _{gs}		---	0.45	---	
Gate-Drain Charge ^{2,3}	Q _{gd}		---	0.75	---	
Turn-on Delay Time ^{2,3}	T _{d(on)}	V _{DD} =-10V, V _{GEN} =-4.5V, R _{GEN} =3Ω, R _L =5Ω	---	9.8	---	nS
Turn-on Rise Time ^{2,3}	T _r		---	4.9	---	
Turn-off Delay Time ^{2,3}	T _{d(off)}		---	20.5	---	
Turn-off Fall Time ^{2,3}	T _f		---	7	---	
Input Capacitance	C _{iSS}	V _{DS} =-10V, V _{GS} =0V, F=1MHz	---	248	---	pF
Output Capacitance	C _{oss}		---	42	---	
Reverse Transfer Capacitance	C _{rSS}		---	31	---	
Drain-Source Diode Characteristics And Maximum Ratings						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Continuous Source Current	I _S	V _G =V _D =0V, Force Current	---	---	-2.5	A
Pulsed Source Current	I _{SM}		---	---	-10	A
Diode Forward Voltage	V _{SD}	V _{GS} =0V, I _S =-2.5A, T _J =25℃	---	---	-1.2	V



Typical Performance Characteristics




Figure1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Ambient Temperature





Figure.11: Maximum Effective Transient Thermal Impedance, Junction-to-Ambient

SOT23 PACKAGE INFORMATION



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.000	0.035	0.039
A1	0.000	0.100	0.000	0.004
b	0.300	0.500	0.012	0.020
c	0.090	0.110	0.003	0.004
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP.		0.037 TYP.	
e1	1.800	2.000	0.071	0.079
L	0.550 REF.		0.022 REF.	
L1	0.300	0.500	0.012	0.020
θ	1°	7°	1°	7°