

BTA60-1600BW 60A TRIAC

Rev.A.2.0

DESCRIPTION


The BTA60-1600BW triac is suitable for general purpose AC switching. It can be used as an ON/OFF function in applications such as heating regulation, induction motor starting circuits, for phase control operation in light dimmers, motor speed controllers. This snubberless triac is especially recommended for use on inductive loads. And provides a rated insulation voltage of 2500 VRMS. Package TO-3P is RoHS compliant.

MAIN FEATURES

Symbol	Value	Unit
$I_{T(RMS)}$	60	A
V_{DRM}/V_{RRM}	1600	V
$I_{GT\ I\ II/III}$	50/50/50	mA

ABSOLUTE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Storage junction temperature range	T_{stg}	-40~150	°C
Operating junction temperature range	T_j	-40~125	°C
Repetitive peak off-state voltage ($T_j=25^{\circ}C$)	V_{DRM}	1600	V
Repetitive peak reverse voltage ($T_j=25^{\circ}C$)	V_{RRM}	1600	V
RMS on-state current ($T_c \leq 78^{\circ}C$)	$I_{T(RMS)}$	60	A
Non repetitive surge peak on-state current (full cycle, $t_p=20ms$, $T_j=25^{\circ}C$)	I_{TSM}	600	A
Non repetitive surge peak on-state current (full cycle, $t_p=16.6ms$, $T_j=25^{\circ}C$)		660	A
I^2t value for fusing ($t_p=10ms$, $T_j=25^{\circ}C$)	I^2t	1800	A ² s
Critical rate of rise of on-state current ($I_G=2 \times I_{GT}$, $f=100Hz$, $T_j=125^{\circ}C$)	di/dt	100	A/ μs
Peak gate current ($t_p=20\mu s$, $T_j=125^{\circ}C$)	I_{GM}	8	A
Average gate power dissipation ($T_j=125^{\circ}C$)	$P_{G(AV)}$	0.5	W
Peak gate power	P_{GM}	10	W
Peak pulse voltage ($T_j=25^{\circ}C$, non-repetitive, off-state)	V_{PP}	2	kV



BTA60-1600BW 60A TRIAC

Rev.A.2.0

ELECTRICAL CHARACTERISTICS (T_j=25°C unless otherwise specified)

Symbol	Test Condition	Quadrant	Value		Unit
I _{GT}	V _D =12V R _L =33Ω	I - II -III	MAX.	50	mA
V _{GT}		I - II -III	MAX.	1.3	V
V _{GD}	V _D =V _{DRM} T _j =125°C R _L =3.3KΩ	I - II -III	MIN.	0.2	V
I _L	I _G =1.2I _{GT}	I -III	MAX.	120	mA
		II		120	
I _H	I _T =1A		MAX.	80	mA
dV/dt	V _D =1070V Gate Open T _j =125°C		MIN.	1500	V/μs
(dI/dt) _c	(dV/dt) _c =20V/μs T _j =125°C		MIN.	28	A/ms
t _{on}	I _G =80mA I _A =400mA I _R =40mA T _j =25°C		TYP.	7	μs
t _{off}				100	

STATIC CHARACTERISTICS

Symbol	Parameter		Value(MAX.)	Unit
V _{TM}	I _{RM} =85A t _p =380μs	T _j =25°C	1.75	V
V _{TO}	Threshold voltage	T _j =125°C	0.71	V
R _D	Dynamic resistance	T _j =125°C	24	mΩ
I _{DRM}	V _D =V _{DRM} V _R =V _{RRM}	T _j =25°C	20	μA
I _{RRM}		T _j =125°C	12	mA

THERMAL RESISTANCES

Symbol	Parameter	Value	Unit
R _{th(j-c)}	junction to case (AC)	0.5	°C/W
R _{th(j-a)}	junction to ambient (AC)	50	°C/W

BTA60-1600BW 60A TRIAC

Rev.A.2.0

FIG.1 Maximum power dissipation versus RMS on-state current




FIG.2: RMS on-state current versus case temperature




FIG.3: Surge peak on-state current versus number of cycles




FIG.4: On-state characteristics




FIG.5: Non-repetitive surge peak on-state current for a sinusoidal pulse with width $t_p < 20ms$, and corresponding value of I^2t ($di/dt < 100A/\mu s$)






FIG.6: Relative variations of gate trigger current, holding current and latching current versus junction temperature



BTA60-1600BW 60A TRIAC



Rev.A.2.0

PACKAGE MECHANICAL DATA



Ref.	Dimensions					
	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	4.40		4.60	0.173		0.181
B	1.45		1.55	0.057		0.061
C	14.35		15.60	0.565		0.614
D	0.50		0.70	0.020		0.028
E	2.70		2.90	0.106		0.114
F	15.80		16.50	0.622		0.650
G	20.40		21.10	0.803		0.831
H	15.10		15.50	0.594		0.610
J	5.40		5.65	0.213		0.222
K	1.10		1.40	0.043		0.055
L	1.25		1.45	0.049		0.057
P	2.80		3.00	0.110		0.118
R		4.35			0.171	
M	12.37		12.77	0.487		0.503

MARKING


	
---	--

PACKAGE	OUTLINE	TUBE (PCS)	INNER BOX (PCS)	PER CARTON
TO-3P	TUBE	30	450	2,250

BTA60-1600BW 60A TRIAC

Rev.A.2.0

NAMING SCHEME



Document Revision History

Date	Revision	Changes
Jun.11, 2025	A.2.0	Last updated

Information furnished is believed to be accurate and reliable. However, ShenZhen AnKingYuan Electronic assumes no responsibility for the consequences of use of such information nor for any infringement of patents or other rights of third parties which may result from its use. Specifications mentioned in this publication are subject to change without notice. This publication supersedes and replaces all information previously supplied.



is a registered trademark of ShenZhen AnKingYuan Electronic.

@2013 ShenZhen AnKingYuan Electronic - Printed in ShenZhen - All Rights Reserved.