

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2006
© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST
J	-


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED	03SEP2009	T.K	M.K






SCALE 1:2






SCALE 1:2



RECOMMENDED PANEL HOLE PATTERN
推奨パネル取付寸法



RoHS COMPLIANT

ITEM	DESCRIPTION	QTY	MATERIAL	FINISH	REMARK
6	アダプタスタビライザ ADAPTER STABILIZER	1	合成樹脂 PLASTIC	無し NONE	UL94V-0
5	メタルプレート METAL PLATE	(1)	ステンレス鋼 STAINLESS STEEL	無し NONE	
4	サポートハウジング SUPPORT HOUSING	12	合成樹脂 PLASTIC	無し NONE	UL94V-0
3	タッピングスクリュー TAPPING SCREW L=8	2	鋼 STEEL	3価クロメート TRIVALENT CHROMATE	
2	コンタクト 0.64x0.4 CONTACT	(156)	ベリリウム銅 BERYLLIUM COPPER	ニッケル下地金メッキ Au OVER Ni PL.	
1	ハウジングリセアッシー HOUSING RECE ASSY	1	ナイロン樹脂 NYLON RESIN	無し NONE	UL94V-0

-1;AS SHOWN
本図

1.PLATING:MATING AREA;1.27μmMIN GOLD OVER 1.27μmMIN NICKEL
SOLDER LEG AREA;GOLD FLASH OVER 1.27μmMIN NICKEL
OTHERS;1.27μmMIN NICKEL

1.めっき:接触部:ニッケル下地1.27μmMINの上に金1.27μmMIN
半田付部:ニッケル下地1.27μmMINの上に金フラッシュ
その他:ニッケル1.27μmMIN

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.3
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±3°

MATERIAL SEE TABLE
FINISH SEE TABLE

DWN	K.SAKAI	18JAN2006
CHK	E.TAKEMASA	18JAN2006
APVD	M.KIMURA	18JAN2006
PRODUCT SPEC	108-5483	
APPLICATION SPEC	-	
WEIGHT	75g	

Tyco Electronics
Tyco Electronics Corporation
Kawasaki, Japan

NAME
M-ZIF CONN RECE
156P SHORT SOLDER TYPE

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	C-5353177	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV D